





## ANSMANN FL4500R

- ANSMANN Luminary Flex rechargeable work floodlight with 50 W SMD LEDs and a lighting power of up to 4.500 lumens
- Three brightness levels can be selected via the on/off switch always optimum illumination for the task at hand
- Homogeneous illumination is ideal for working in indoor and outdoor areas
- Can also be used without a power outlet Integrated li-ion rechargeable battery pack (Li-Ion 11.1V / 6600 mAh) with safety electronics to protect against over-loading and deep-discharge
- LED rechargeable battery capacity indication check the available capacity
- Including suitable mains adapter for charging the rechargeable battery pack
- Splash-proof (IP54) can be used indoors and out
- Very pleasant LED light with a colour temperature of 5000K (daylight)
- Versatile use thanks to the sturdy adjustment bracket the adjustable support can be adjusted up to 80°, and the light head a full 360°!

## **INFORMATION**

 Product name
 FL4500R

 Part No.
 1600-0402

 EAN-Code
 4013674172627

 Customs tariff number
 94054239000

**Product content** FL4500R, mains adapter, operating

instructions:

