

Item no.: 2002-1402
Product description: 4-conductor through terminal block suitable for Ex e applications



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Current intensity EN	32 A
Product group	22 (TOPJOB S RAIL-MOUNTED TERMINAL BLOCKS)
Cross section [mm ²]	0.25 - 2.5 mm ²
Cross section [AWG]	22 - 12 AWG
Connection method	CAGE CLAMP®S Connection
Cross section [mm ²]	0.25 - 4 mm ²
Cross section [AWG]	22 - 12 AWG
Wiring method	s + f-st
Connection method	CAGE CLAMP®S Connection
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	24 A
Rated voltage EN (Ex e II)	550 V
Nominal current (Ex e II)	22 A
Weight	6.411 g
Color	orange
Wiring type	Front-entry
No. of connection Points	4

No. of potentials
Height
Height

1
33 mm
1.299 in



Width	5.2 mm
Width	0.205 in
Depth	70 mm
Depth	2.76 in
Strip length from	10 mm
Strip length to	12 mm
Strip length	0.43 in
Customs Tariff No.	85369010
Country of Origin	Deutschland
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
2002-1402	ABS	05-HG476175/3-PDA	800	24	0,5-4
2002-1402	AEX	E185892	550	20	22-12
2002-1402	CCA	NL6387	800	24/32	0,2-2,5/4
2002-1402	CSA	154112-1536069	600	20	22-12
2002-1402	DNV	E-10423	800	24	0,5-4
2002-1402	GL	26187-05HH	800	24	0,25-2,5
2002-1402	KEMA	NL2116586.02	800	24	0,5-4
2002-1402	LR	91/20112(E6)	800	24	0,5-4
2002-1402	PRS	TE/1718/880590/08	800	24	0,2-4
2002-1402	PTB	IECEXPTB03.0004U	550	22	0,2-4
2002-1402	PTB	PTB03Atox1162U	550	22	0,2-4
2002-1402	RosTest	8189158	550	22	0,2-4
2002-1402	UR	E45172	600	20	22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected