

ECH-4G



Specifications

ETI Code	001101060
Description	ECH-4G
Weight	.46
Level	Wall-mounted plastic boards IP65
Rows	1
Mounting type	Surface mounted
Type of door	Transparent door
Frame size	4
IP rating	IP65
Catalogue Group	ECH wall mounted plastic distribution boxes IP65

Online product page 

Other documentation



Technical data catalogue
EU declaration



ETIM international classification

Mounting method	
Colour	Grey
Width	128mm
Height	201mm
Depth	120mm
RAL-number	
With mounting plate	
Built-in depth	mm
Number of rows	1
Type of cover	
EMC-version	true
Extension possible	
Internal depth	mm
DIN-rail	true
Material housing	Plastic
Width in number of modular spacings	4
Degree of protection (IP), front side	IP65
Type of door	Transparent door
Degree of protection (IP)	IP65
Transparent cover/door	

With lock

Cover model

Frame size acc. to IEC

Dimension drawing

Dimensions

type	Dimensions						Max. allowed power losses when Max. number of devices are installed
	A	B	C	D	E	F	Pde
ECH-4G	201 mm	128 mm	120 mm	-	78 mm	111 mm	10W
ECH-8G	201 mm	202 mm	120 mm	-	100 mm	140 mm	13W
ECH-12PT	259 mm	319 mm	144 mm	-	210 mm	130 mm	16W
ECH-24PT	384 mm	319 mm	144 mm	125 mm	210 mm	255 mm	24W
ECH-36PT	508 mm	319 mm	144 mm	125 mm	210 mm	380 mm	26W

