



NOTE:

- \* Base Material: ABS Resin,Black
- \* Flammability Rating: UL94-HB or Custom Made
- \* Temperature Range: -10°C to 100°C
- \* Wire: UL1007 26 AWG,300V,80°C  
150±5mm,Strip and Tin 5±1mm
- \* Snaps: Brass,Nickel Plated
- \* Rivet: Brass, Nickel Plated
- \* RoHS COMPLIANT

**NINGBO KLS ELECTRONIC CO.,LTD**

PART NAME

**TWO "UM-9V" CELLS HOLDER**

PROJECTIVE 	TOLERANCES [MM]	DRN BY	DATE
	DECIMAL [±.20]	HYQ	2018 07 18
	ANGULAR ±0.50°	XGY	SCALE 1X
UNLESS OTHERWISE SPECIFIED		DWG NO.	L-KLS5-TBH-9V-A-W