



XIAMEN OLINK IMPORT & EXPORT CO., LTD

Junction Box Series

UTJ5 导轨式接线盒系列 UTJ5 Rail type junction box series



- 加厚铝制导体，重量轻、截面大、耐腐蚀性强。
- 全新尼龙PA66，能够承受较高的温度和压力，在各种恶劣环境下保持良好的性能。
- 带内六角螺丝，接线前拧开螺丝，接入导线后拧紧螺丝，完成接线，牢固耐用。
- Thick aluminum conductor, lightweight, large cross-section, and strong corrosion resistance.
- The brand new nylon PA66 can withstand high temperatures and pressures, maintaining good performance in various harsh environments.
- Equipped with hexagonal screws, unscrew the screws before wiring, tighten the screws after connecting the wires, and complete the wiring with firmness and durability.

型号 Item no.	额定电流 Current (A)	额定电压 Voltage (V)	尺寸 Dimensions (mm)	导线截面 Wire section (mm ²)	螺丝规格 Screw specs	进线方式 Entry method	产品颜色 Product color
UTJ5-16	63	800	14x44x40	16	M6	一进一出 1 in, 1 out	<div style="display: flex; flex-direction: column; align-items: center;"> <div style="display: flex; align-items: center; margin-bottom: 5px;"> 黄绿 PE </div> <div style="display: flex; align-items: center; margin-bottom: 5px;"> 灰色 GY </div> <div style="display: flex; align-items: center;"> 灰蓝 BE </div> </div>
UTJ5-35	120	800	15.8x46x40	35	M8	一进一出 1 in, 1 out	
UTJ5-35-2	120	800	27.8x46x40	2x35	M6	一进三出 1 in, 3 out	
UTJ5-50	145	800	17.8x50x43.3	50	M10	一进一出 1 in, 1 out	
UTJ5-50-2	145	800	31.8x50x43.3	2x50	M10	一进三出 1 in, 3 out	
UTJ5-50-3	145	800	44.8x50x43.3	3x50	M10	一进五出 1 in, 5 out	
UTJ5-95	220	800	24x91.4x49.2	95	M14	一进一出 1 in, 1 out	
UTJ5-95-2	220	800	42x91.4x49.2	2x95	M14	一进三出 1 in, 3 out	
UTJ5-150	240	800	28.8x101.6x60	150	M18	一进一出 1 in, 1 out	
UTJ5-240	380	800	36x130.7x66.7	240	M20	一进一出 1 in, 1 out	