



NOTE:

- * Zinc alloy die cast housing and cylinder, Bright nickel plated standard.
- * 4 disc tumbler mechanism, Brass keys, nickel plated.
- * Golden plated contacts and terminals.
- * All keyed alike.
- * "12" position(8-1,4-5 ON), "1:30" position (1-2,5-6 ON), "10:30" position(7-8,3-4 ON).
- * Key no: A126, Key Pull at 12,10:30 and 1:30;

SPECIFICATION:

- * UL approval standard.
- * Contact Rating: 4A 125VAC, 2A 250VAC.
- * Contact Resistance: 50Milli-Ohms Max.
- * Insulation Resistance: 500 Meg-Ohms Min. (500VDC)
- * Dielectric Strength: 1500 VAC-1 Minute.

DESCRIPTION	SWITCH LOCK	
PART NO.	S2011J-2-8	
MATERIAL	ZDC2	
NOTE		
APPROVED BY	CHECKED BY	DRAWN BY
TOLERANCES	UNIT	SCALE
± 0.1 ± 0.2 ± 0.3 ± 0.5 ± 1.0 ± 2.0 ± 3.0 ± 5.0 ± 10.0	mm	1:1



JIN TAY INDUSTRIES CO., LTD.

REV. NO.	COORDINATES	WAS	NEW	DATE	BY	REV. A	WT.	DATE
1							g	17.11.28