


KEMET Part Number: ALT22A333CD016 **Obsolete**
(A663EJ333M016A)

ALT22, Aluminum Electrolytic, 33,000 uF, 20%, 16 VDC, -40/+85°C



Dimensions	
D	35mm +/-1mm
L	55mm +/-2mm
S	10mm +/-0.1mm
LL	10mm +/-0.5mm

Packaging Specifications	
Weight:	75 g
Sleeving:	Yes
Packaging:	Bulk, Bag

General Information	
Supplier:	KEMET
Series:	ALT22
Dielectric:	Aluminum Electrolytic
Description:	Solder Tag, Aluminum Electrolytic
Features:	Solder Tag
RoHS:	Yes
Lead:	2 Flying Leads Solder Tags
AEC-Q200:	No
Miscellaneous:	Non-Standard Part, Contact KEMET For Availability
Notes:	Dimensions D And L Include Sleeving

Specifications	
Capacitance:	33,000 uF
Capacitance Tolerance:	20%
Voltage DC:	16 VDC, 18.4 VDC (Surge)
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	18000 Hrs
Leakage Current:	3168 uA (5min 20°C)