


Capacitor, film, Metallized Polypropylene, 5 uF, +/-5% Tol, -40/+85C, Power, 550 VAC



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	57.5	NOM
H	50	NOM
T	35	NOM
S	37	

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	21

General Information	
Supplier:	KEMET
Dielectric:	Metallized Polypropylene
Application:	Power
Style:	Radial Box
Features:	IGBT Circuit
RoHS:	Yes

Specifications	
Capacitance:	5 uF
Voltage:	850 V
Tolerance:	+/-5%
Voltage AC:	550 VAC
Rated Temperature:	70C
Temperature Range:	-40/+85C
Maximum dVdT:	469 v/us
Current/Ripple Current:	42 Amps (100kHz 70C)
Current/Ripple Current:	2347 Amps (Peak)
Resistance/ESR:	1.9 mOhms (100kHz)
Inductance:	48 nH
Miscellaneous:	Kemet Style B Tabs