




# DA series

Right Angle Dual in Line Switches

General



- Raised actuators
- Even and odd pole numbers
- Right Angle
- Gold contacts for high reliability



## General Specifications

- Contact Rating 25mA 24VDC
- Contact Resistance 50mΩ max.
- Insulation Resistance 100MΩ min, 500VDC
- Dielectric Strength 500VAC/1 Minute
- Operating Force 1000gf max
- Travel 2mm
- Operating Life 2,000 Cycles
- Operating Temperature -20°C to +70°C
- Storage Temperature -40°C to +85°C

## Materials

- Case: Black glass fibre filled PBT
- Cover: Red glass fibre filled PBT
- Actuator: White glass fibre filled PBT
- Terminals/contact: Gold plated phosphor bronze
- Terminal seal: Epoxy
- Tape seal: Polyester film
- UL94-V0


## Packaging

- IC Tube (see chart on the next page)

Overview

Model No	No. pos.	Dim "A"	Dim. "B"
DA-02	2	6,44 (.253)	2,54 (.100)
DA-03	3	8,89 (.350)	5,08 (.200)
DA-04	4	11,52 (.453)	7,62 (.300)
DA-05	5	14,06 (.553)	10,16 (.400)
DA-06	6	16,60 (.653)	12,70 (.500)
DA-07	7	19,14 (.753)	15,24 (.600)
DA-08	8	21,68 (.853)	17,78 (.700)
DA-09	9	24,22 (.953)	20,32 (.800)
DA-10	10	26,76 (1.053)	22,86 (.900)
DA-12	12	31,84 (1.253)	27,94 (1.100)

Top tape sealed : add "T" after model number.




Note: The company reserves the right to change specifications without notice.

# DA series

Right Angle Dual in Line Switches

Overview Cont



Packaging



- Supplied in standard IC tubes

DA-02 73pcs	DA-02-T 70pcs
DA-03 52pcs	DA-03-T 50pcs
DA-04 40pcs	DA-04-T 39pcs
DA-05 33pcs	DA-05-T 32pcs
DA-06 28pcs	DA-06-T 28pcs
DA-07 24pcs	DA-07-T 24pcs
DA-08 21pcs	DA-08-T 21pcs
DA-09 19pcs	DA-09-T 19pcs
DA-10 17pcs	DA-10-T 17pcs
DA-12 14pcs	DA-12-T 14pcs