nay.com Vishay

Standard Thick Film Chip Resistors




LINKS TO ADDITIONAL RESOURCES



D/CRCW e3 standard thick film chip resistors are the perfect choice for most fields of modern electronics where high reliability and stability are of major concern. Typical applications include automotive, telecommunications, and industrial.

FEATURES





- 2 mm pitch packaging option for 0603 size
- AEC-Q200 qualified
- Material categorization: for definitions of compliance please see www.vishav.com/doc?99912

APPLICATIONS

- Automotive
- Industrial
- Telecommunication

DESCRIPTION	D10/CRCW0402 e3	D11/CRCW0603 e3	D12/CRCW0805 e3	D25/CRCW1206 e3	CRCW1210 e3	CRCW1218 e3	CRCW2010 e3	CRCW2512 e3
Imperial size	0402	0603	0805	1206	1210	1218	2010	2512
Metric size code	RR1005M	RR1608M	RR2012M	RR3216M	RR3225M	RR3246M	RR5025M	RR6332M
Resistance range	1 Ω to 10 M Ω ; jumper (0 Ω) $ \begin{array}{c} 1 \Omega \text{ to} \\ 2.2 \text{ M}\Omega; \\ \text{jumper} \\ (0 \Omega) \end{array} $ 1 Ω to 10 N jumper (0 Ω)							
Resistance tolerance				± 5 %; ± 1 %				
Temperature coefficient			± 200	ppm/K; ± 100 pp	m/K			
Rated dissipation, P_{70} (1)	0.063 W	0.10 W	0.125 W	0.25 W	0.5 W	1.0 W	0.75 W	1.0 W
Operating voltage, U _{max.} AC _{RMS} /DC	50 V	75 V	150 V	200 V	200 V	200 V	400 V	500 V
Permissible film temperature, <i>v</i> _{F max.} (1)		155 °C						
Operating temperature range		-55 °C to +155 °C						
Max. resistance change at P_{70} for resistance range, $ \Delta R/R $, after ⁽²⁾ :								
1000 h				≤ 1 %				
8000 h		≤ 2 %						
Permissible voltage against ambient (insulation):								
1 min, U _{ins}	75 V	100 V	200 V	300 V	300 V	300 V	300 V	300 V
Failure rate: FIT _{observed}	≤ 0.1 x 10 ⁻⁹ /h							

Notes

Revision: 05-Aug-2022 1 Document Number: 20035

⁽¹⁾ Please refer to "Application Information" below

⁽²⁾ Apply to components with stability class 1



APPLICATION INFORMATION

When the resistor dissipates power, a temperature rise above the ambient temperature occurs, dependent on the thermal resistance of the assembled resistor together with the printed circuit board. The rated dissipation applies only if the permitted film temperature is not exceeded.

These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime.

TYPE / SIZE	TCR	TOLERANCE	RESISTANCE	E-SERIES
	± 200 ppm/K	± 5 %	1 Ω to 10 M Ω	E24
D10/CRCW0402 e3	± 100 ppm/K	± 1 %	1 Ω to 10 M Ω	E24; E96
	Jumper, <i>I</i> _{max.} = 1.5 A	≤ 20 mΩ	0 Ω	-
	± 200 ppm/K	± 5 %	1 Ω to 10 M Ω	E24
D11/CRCW0603 e3	± 100 ppm/K	± 1 %	1 Ω to 10 MΩ	E24; E96
	Jumper, I _{max.} = 2.0 A	≤ 20 mΩ	0 Ω	-
	± 200 ppm/K	± 5 %	1 Ω to 10 MΩ	E24
D12/CRCW0805 e3	± 100 ppm/K	± 1 %	1 Ω to 10 MΩ	E24; E96
	Jumper, <i>I</i> _{max.} = 2.5 A	≤ 20 mΩ	0 Ω	-
	± 200 ppm/K	± 5 %	1 Ω to 10 M Ω	E24
D25/CRCW1206 e3	± 100 ppm/K	± 1 %	1 Ω to 10 MΩ	E24; E96
	Jumper, <i>I</i> _{max.} = 3.5 A	≤ 20 mΩ	0 Ω	-
	± 200 ppm/K	± 5 %	1 Ω to 10 M Ω	E24
CRCW1210 e3	± 100 ppm/K	± 1 %	1 Ω to 10 M Ω	E24; E96
	Jumper, <i>I</i> _{max.} = 5.0 A	\leq 20 m Ω	0 Ω	-
	± 200 ppm/K	± 5 %	1 Ω to 2.2 M Ω	E24
CRCW1218 e3	± 100 ppm/K	± 1 %	1 Ω to 2.2 MΩ	E24; E96
	Jumper, <i>I</i> _{max.} = 7.0 A	≤ 20 mΩ	0 Ω	-
	± 200 ppm/K	± 5 %	1 Ω to 10 MΩ	E24
CRCW2010 e3	± 100 ppm/K	± 1 %	1 Ω to 10 MΩ	E24 E24; E96 E24 E24; E96 E24 E24; E96 E24 E24; E96 - E24 E24; E96 - E24 E24; E96 E24 E24; E96
	Jumper, I _{max.} = 6.0 A	≤ 20 mΩ	0 Ω	-
	± 200 ppm/K	± 5 %	1 Ω to 10 MΩ	E24
CRCW2512 e3	± 100 ppm/K	± 1 %	1 Ω to 10 MΩ	E24; E96
	Jumper, I _{max.} = 7.0 A	≤ 20 mΩ	0 Ω	-


Note

• The temperature coefficient of resistance (TCR) is not specified for 0 Ω jumpers



www.vishay.com

PACKAGING							
TYPE / SIZE	CODE	QUANTITY	PACKAGING STYLE	WIDTH	PITCH	PACKAGING DIMENSIONS	
D10/CRCW0402 e3	ED = ET7	10 000		8 mm	2 mm	Ø 180 mm / 7"	
D10/ChCW0402 e3	EE = EF4	50 000		0 111111		Ø 330 mm / 13"	
	EI = ET2	5000				Ø 180 mm / 7"	
	ED = ET3	10 000			2 mm	Ø 180 mm / 7"	
	EL = ET4	20 000			2 111111	Ø 285 mm / 11.25"	
D11/CRCW0603 e3	EE = ET8	50 000		8 mm		Ø 330 mm / 13"	
	EA = ET1	5000	Paper tape acc. to		4 mm	Ø 180 mm / 7"	
	EB = ET5	10 000				Ø 285 mm / 11.25"	
	EC = ET6	20 000				Ø 330 mm / 13"	
	EA = ET1	5000	IEC 60286-3, Type 1a	8 mm	4 mm	Ø 180 mm / 7"	
D12/CRCW0805 e3	EB = ET5	10 000				Ø 285 mm / 11.25"	
	EC = ET6	20 000				Ø 330 mm / 13"	
	EA = ET1	5000			4 mm	Ø 180 mm / 7"	
D25/CRCW1206 e3	EB = ET5	10 000		8 mm		Ø 285 mm / 11.25"	
	EC = ET6	20 000				Ø 330 mm / 13"	
	EA = ET1	5000				Ø 180 mm / 7"	
CRCW1210 e3	EB = ET5	10 000		8 mm	4 mm	Ø 285 mm / 11.25"	
	EC = ET6	20 000				Ø 330 mm / 13"	
CRCW1218 e3	EK = ET9	4000		12 mm	4 mm	Ø 180 mm / 7"	
CRCW2010 e3	EF = E02	4000	Blister tape acc. to	12 mm	4 mm	Ø 180 mm / 7"	
CDCW0510 c2	EG = E67	2000	IEC 60286-3, Type 2a	10	8 mm	Ø 100 mm / 7"	
CRCW2512 e3	EH = E82	4000		12 mm	4 mm	Ø 180 mm / 7"	





www.vishay.com

Vishav

DESCRIPTION

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. A cermet film layer and a glass-over are deposited on a high grade (Al_2O_3) ceramic substrate with its prepared inner contacts. A special laser is used to achieve the target value by smoothly fine trimming the resistive layer without damaging the ceramics. The resistor elements are covered by a protective coating designed for electrical, mechanical and climatic protection. The terminations receive a final pure tin on nickel plating.

The result of the determined production is verified by an extensive testing procedure on 100 % of the individual chip resistors. Only accepted products are laid directly into the tape in accordance with **IEC 60286-3 Type 1a and Type 2a** (1).

ASSEMBLY

The resistors are suitable for processing on automatic SMD assembly systems. They are suitable for automatic soldering using wave, reflow or vapor phase as shown in **IEC 61760-1** ⁽¹⁾. The encapsulation is resistant to all cleaning solvents commonly used in the electronics industry, including alcohols, esters and aqueous solutions. The suitability of conformal coatings, potting compounds and their processes, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system.

The resistors are RoHS-compliant, the pure tin plating provides compatibility with lead (Pb)-free and lead-containing soldering processes. Solderability is specified for 2 years after production or requalification. The permitted storage time is 20 years. The immunity of the plating against tin whisker growth has been proven under extensive testing.

MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances:

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein (2)
- The Global Automotive Declarable Substance List (GADSL) ⁽³⁾
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) (4) for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see www.vishay.com/how/leadfree.

Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at www.vishay.com/doc?49037.

APPROVALS

The resistors are qualified according to AEC-Q200.

Where applicable, the resistors are tested in accordance with **EN 140401-802** which refers to **EN 60115-1**, **EN 60115-8** and the variety of environmental test procedures of the **IEC 60068** ⁽¹⁾ series.

RELATED PRODUCTS

For more information about products with better TCR and tighter tolerance please refer to the "Lead (Pb)-Free Thick Film, Rectangular, Semi-Precision Chip Resistors" datasheet (www.vishav.com/doc?20036).

The D/CRCW with SnPb termination plating is designed for applications where lead bearing terminations are mandatory. For ordering D/CRCW with SnPb terminations please refer to latest edition of datasheet D/CRCW (www.vishay.com/doc?20008).


Notes

- (1) The quoted IEC standards are also released as EN standards with the same number and identical contents
- (2) The IEC 62474 list of declarable substances is maintained in a dedicated database, which is available at http://std.iec.ch/iec62474
- (3) The Global Automotive Declarable Substance List (GADSL) is maintained by the American Chemistry Council and available at www.gadsl.org
- (4) The SVHC list is maintained by the European Chemical Agency (ECHA) and available at http://echa.europa.eu/candidate-list-table




FUNCTIONAL PERFORMANCE

Single Pulse




Maximum pulse load, single pulse; applicable if $\overline{P} \to 0$ and n < 1000 and $\hat{U} = \hat{U}_{\text{max}}$; for permissible resistance change equivalent to 8000 h operation

Continuous Pulse



Maximum pulse load, continuous pulses; applicable if $\overline{P} \le P$ (ϑ_{amb}) and $\hat{U} = \hat{U}_{max}$; for permissible resistance change equivalent to 8000 h operation


Pulse Voltage




Maximum pulse voltage, single and continuous pulses; applicable if $\hat{P} = \hat{P}_{max}$; for permissible resistance change equivalent to 8000 h operation




Derating



Non-Linearity



Current Noise







TESTS AND REQUIREMENTS

All executed tests are carried out in accordance with the following specifications:

EN 60115-1, generic specification

EN 60115-8 (successor of EN 140400), sectional specification

EN 140401-802, detail specification

IEC 60068-2-xx, test methods

The parameters stated in the Test Procedures and Requirements table are based on the required tests and permitted limits of EN 140401-802. The table presents only the most important tests, for the full test schedule refer to the documents listed above. However, some additional tests and a number of improvements against those minimum requirements have been included.

The testing also covers most of the requirements specified by EIA/IS-703 and JIS-C-5201-1.

The tests are carried out under standard atmospheric conditions in accordance with IEC 60068-1, 4.3, whereupon the following values are applied:

Temperature: 15 °C to 35 °C Relative humidity: 25 % to 75 %

Air pressure: 86 kPa to 106 kPa (860 mbar to 1060 mbar).

A climatic category LCT / UCT / 56 is applied, defined by the lower category temperature (LCT), the upper category temperature (UCT), and the duration of exposure in the damp heat, steady state test (56 days). The components are mounted for testing on boards in accordance with EN 60115-8, 2.4.2 unless otherwise specified.

TEST PROCEDURES AND REQUIREMENTS									
	IEC		PROOFFILE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)					
EN 60115-1	60068-2	TEST	PROCEDURE	STABILITY CLASS 1 OR BETTER	STABILITY CLASS 2 OR BETTER				
CLAUSE	METHOD		Stability for product types:	1 Ω to 10 MΩ					
			D/CRCW e3	1 52 10	TO IVISZ				
4.5	-	Resistance	-	± 1 %	± 5 %				
4.8	-	Temperature coefficient	At (20 / -55 / 20) °C and (20 / 155 / 20) °C	± 100 ppm/K	± 200 ppm/K				
4.25.1	-	Endurance at 70 °C	$U = \sqrt{P_{70} \times R}$ or $U = U_{\text{max.}}$ whichever is the less severe; 1.5 h on; 0.5 h off						
			70 °C; 1000 h	$\pm (1 \% R + 0.05 \Omega)$	± (2 % R + 0.1 Ω)				
			70 °C; 8000 h	± (2 % R + 0.1 Ω)	± (4 % R + 0.1 Ω)				
4.25.3	-	Endurance at upper category temperature	155 °C; 1000 h	± (1 % R + 0.05 Ω)	± (2 % R + 0.1 Ω)				
4.24	78 (Cab)	Damp heat, steady state	(40 ± 2) °C; 56 days; (93 ± 3) % RH	± (1 % R + 0.05 Ω)					
4.37	67 (Cy)	Damp heat, steady state, accelerated	(85 ± 2) °C; (85 ± 5) % RH; $U = \sqrt{0.1 \times P_{85} \times R} \le 100 \text{ V};$ 1000 h	± (1 % R + 0.05 Ω)	± (2 % R + 0.1 Ω)				
4.23	-	Climatic sequence:							
4.23.2	2 (Bb)	Dry heat	125 °C; 16 h						
4.23.3	30 (Db)	Damp	55 °C; 24 h; ≥ 90 % RH; 1 cycle						
4.23.4	1 (Ab)	Cold	-55 °C; 2 h	± (1 % R + 0.05 Ω)	± (2 % R + 0.1 Ω)				
4.23.5	13 (M)	Low air pressure	8.5 kPa; 2 h; (25 ± 10) °C	_ (, , , , , , , , , , , , , , , , , ,	_ (_ ,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,				
4.23.6	30 (Db)	Damp heat, cyclic	55 °C; 5 days; > 90 % RH; 5 cycles						
4.23.7	-	DC load	$U = \sqrt{P_{70} \times R} \le U_{\text{max.}}$; 1 min						
-	1 (Aa)	Cold	-55 °C; 2 h	$\pm (0.25 \% R + 0.05 \Omega)$					
4.19	14 (Na)	Rapid change of temperature	30 min. at -55 °C and 30 min. at 125 °C 1000 cycles	\pm (1 % R + 0.05 Ω) no visible damage					
4.13	-	Short time overload	$U = 2.5 \text{ x } \sqrt{P_{70} \text{ x } R} \le 2 \text{ x } U_{\text{max.}};$ whichever is the less severe; 5 s	\pm (2 % R + 0.05 Ω)					
4.27	-	Single pulse high voltage overload	Severity no. 4: $U = 10 \times \sqrt{P_{70} \times R}$ or $U = 2 \times U_{\text{max.}}$; whichever is the less severe; 10 pulses 10 µs / 700 µs	\pm (1 % R + 0.05 Ω) no visible damage					

www.vishay.com Vishay


	ROCEDU	TEST		REQUIREMENTS PERMISSIBLE CHANGE (△R)			
EN 60115-1	1EC 60068-2 (1) TEST		PROCEDURE	STABILITY CLASS 1 OR BETTER	STABILITY CLASS 2 OR BETTER		
CLAUSE	METHOD		Stability for product types:	1.04-	10 MO		
			D/CRCW e3	1 Ω to 10 M Ω			
4.39	-	Periodic electric overload	$U = \sqrt{15 \times P_{70} \times R}$ or $U = 2 \times U_{\text{max.}}$; whichever is the less severe; 0.1 s on; 2.5 s off; 1000 cycles	± (1 % R + 0.05 Ω) no visible damage			
4.38	-	Electrostatic discharge (human body model)	IEC 61340-3-1 ⁽¹⁾ ; 3 positive + 3 negative discharges; ESD voltage acc. to size	± (1 % R + 0.05 Ω)			
4.22	6 (Fc)	Vibration	Endurance by sweeping; 10 Hz to 2000 Hz; no resonance; amplitude \leq 1.5 mm or \leq 200 m/s ² ; 7.5 h	± (0.25 % R + 0.05 Ω) no visible damage	\pm (0.5 % R + 0.05 Ω) no visible damage		
			Solder bath method, SnPb40; non-activated flux (235 ± 5) °C; (2 ± 0.2) s	Good tinning (≥ 95 % covered);			
4.17	58 (Td)	Solderability	Solder bath method, Sn96.5Ag3Cu0.5; non-activated flux (245 ± 5) °C; (3 ± 0.3) s	O ,	e damage		
4.18	58 (Td)	Resistance to soldering heat	Soldering bath method; (260 ± 5) °C; (10 ± 1) s	$\pm (0.25 \% R + 0.05 \Omega)$	$\pm (0.5 \% R + 0.05 \Omega)$		
4.29	45 (XA)	Component solvent resistance	Isopropyl alcohol; +50 °C; method 2	No visible damage			
4.32	21 (Uu ₃)	Shear (adhesion)	CRCW0402 and CRCW0603: 9 N CRCW0805 to CRCW2512: 45 N	No visible damage			
4.33	21 (Ue ₁)	Substrate bending	Depth 2 mm; 3 times	\pm (0.25 % R + 0.05 Ω) no visible damage, no open circuit in bent position			
4.7	-	Voltage proof	$U = 1.4 \times U_{ins}$; 60 s	No flashover or breakdown			
4.35	-	Flammability, needle flame test	IEC 60695-11-5 ⁽¹⁾ ; 10 s	No burning	g after 30 s		

Note

⁽¹⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents




DIMENSIONS



DIMENSIONS AND MASS									
TYPE / SIZE	L (mm)	W (mm)	H (mm)	T1 (mm)	T2 (mm)	MASS (mg)			
D10/CRCW0402 e3	1.0 ± 0.05	0.5 ± 0.05	0.35 ± 0.05	0.25 ± 0.10	0.2 ± 0.10	0.65			
D11/CRCW0603 e3	1.55 + 0.10 / - 0.05	0.85 ± 0.10	0.45 ± 0.05	0.3 ± 0.20	0.3 ± 0.20	2			
D12/CRCW0805 e3	2.0 + 0.20 / - 0.10	1.25 ± 0.15	0.45 ± 0.05	0.3 + 0.20 / - 0.10	0.3 ± 0.20	5.5			
D25/CRCW1206 e3	3.2 + 0.10 / - 0.20	1.6 ± 0.15	0.55 ± 0.05	0.45 ± 0.20	0.4 ± 0.20	10			
CRCW1210 e3	3.2 ± 0.20	2.5 ± 0.20	0.55 ± 0.05	0.45 ± 0.20	0.4 ± 0.20	16			
CRCW1218 e3	3.2 + 0.10 / - 0.20	4.6 ± 0.15	0.55 ± 0.05	0.45 ± 0.20	0.4 ± 0.20	29.5			
CRCW2010 e3	5.0 ± 0.15	2.5 ± 0.15	0.6 ± 0.10	0.6 ± 0.20	0.6 ± 0.20	25.5			
CRCW2512 e3	6.3 ± 0.20	3.15 ± 0.15	0.6 ± 0.10	0.6 ± 0.20	0.6 ± 0.20	40.5			

SOLDER PAD DIMENSIONS



RECOMMENDED SOLDER PAD DIMENSIONS								
		WAVE SO	LDERING		REFLOW SOLDERING			
TYPE / SIZE	G (mm)	Y (mm)	X (mm)	Z (mm)	G (mm)	Y (mm)	X (mm)	Z (mm)
D10/CRCW0402 e3	=	-	-	-	0.45	0.6	0.6	1.65
D11/CRCW0603 e3	0.65	1.10	1.25	2.85	0.75	0.75	1.00	2.25
D12/CRCW0805 e3	0.90	1.30	1.60	3.50	1.00	0.95	1.45	2.90
D25/CRCW1206 e3	1.40	1.40	1.95	4.20	1.50	1.05	1.80	3.60
CRCW1210 e3	1.80	1.45	2.95	4.70	1.70	1.10	2.80	3.90
CRCW1218 e3	1.80	1.30	5.10	4.40	1.90	1.10	4.90	4.10
CRCW2010 e3	3.40	1.65	2.85	6.70	3.50	1.45	2.80	6.40
CRCW2512 e3	4.60	1.60	3.65	7.80	4.75	1.45	3.50	7.65

Note

The rated dissipation applies only if the permitted film temperature is not exceeded. Furthermore, a high level of ambient temperature or of
power dissipation may raise the temperature of the solder joint, hence special solder alloys or board materials may be required to maintain
the reliability of the assembly.

The given solder pad dimensions reflect the considerations for board design and assembly as outlined e.g. in standards IEC 61188-5-x or in publication IPC-7351. They do not guarantee any supposed thermal properties, particularly as these are also strongly influenced by many other parameters. Still, the given solder pad dimensions will be found adequate for most general applications

Legal Disclaimer Notice



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.