COMPLIANT

HALOGEN

FREE



Vishay General Semiconductor

Ultrafast Plastic Rectifier



PRIMARY CHARACTERISTICS					
I _{F(AV)}	4.0 A				
V_{RRM}	400 V, 600 V				
I _{FSM}	I _{FSM} 150 A				
t _{rr}	50 ns				
V _F at I _F	1.05 V				
T _J max.	175 °C				
Package	DO-201AD				
Circuit configuration	Single				

FEATURES

- Glass passivated pellet chip junction
- Ultrafast reverse recovery time
- Low forward voltage drop
- · Low leakage current
- · Low switching losses, high efficiency
- High forward surge capability
- Solder dip 275 °C max. 10 s, per JESD 22-B106
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

TYPICAL APPLICATIONS

For use in high frequency rectification and freewheeling application in switching mode converters and inverters for consumer, computer, and telecommunication.

MECHANICAL DATA

Case: DO-201AD

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade Base P/N-M3 - halogen-free, RoHS-compliant, and commercial grade

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 and M3 suffix meets JESD 201 class 1A whisker test

Polarity: color band denotes cathode end

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)				
PARAMETER	SYMBOL	MUR440	MUR460	UNIT
Maximum repetitive peak reverse voltage	V_{RRM}	400	600	
Working peak reverse voltage	V_{RWM}	400	600	V
Maximum DC blocking voltage	V _{DC}	400	600	
Maximum average forward rectified current (fig. 1)	I _{F(AV)}	4.0		^
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	150		А
Operating junction and storage temperature range	T _J , T _{STG}	-65 to +175		°C

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)							
PARAMETER	TEST CONDITIONS		SYMBOL	MUR440	MUR460	UNIT	
Maximum instantaneous forward voltage	3.0 A		V _F ⁽¹⁾	1.0	05		
		1.25		V			
	4.0 A	T _J = 25 °C		1.2	28		
Maximum instantaneous reverse current		T _J = 25 °C		10			
at rated DC blocking voltage		T _J = 150 °C	I _R ⁽¹⁾	25	50	μΑ	
Max. reverse recovery time	I _F = 0.5, I _R = 1.0 A, I _{rr} = 0.25 A		t _{rr}	50			
Maximum reverse recovery time	$I_F = 1.0 \text{ A}, \text{ dI/dt} = 50 \text{ A/}\mu\text{s}, V_R = 30 \text{ V}, I_{rr} = 10 \% I_{RM}$		t _{rr}	7	5	ns	
Maximum forward recovery time	I _F = 1.0 A, dI/dt = 100 A/μs, recovery to 1.0 V		t _{fr}	5	0		

Note

⁽¹⁾ Pulse test: $t_p = 300 \mu s$, duty cycle $\leq 2 \%$



Vishay General Semiconductor

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	BOL MUR440 MUR460			
Typical thermal resistance junction to ambient	R _{0JA} (1)	28		°C/W	

Note

⁽¹⁾ Lead length = 1/2" on PCB with 1.5" x 1.5" copper surface

ORDERING INFORMATION (Example)						
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE		
MUR460-E3/54	1.138	54	1400	13" diameter paper tape and reel		
MUR460-E3/73	1.138	73	1000	Ammo pack packaging		
MUR460-M3/54	1.138	54	1400	13" diameter paper tape and reel		
MUR460-M3/73	1.138	73	1000	Ammo pack packaging		

RATINGS AND CHARACTERISTICS CURVES ($T_A = 25$ °C unless otherwise noted)




Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 4 - Typical Reverse Characteristics



Vishay General Semiconductor





Fig. 5 - Typical Junction Capacitance per Leg

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.