

PIN CONTACT, 20 DF ✓ ACTIVE

AMPLIMITE


TE Part # 66507-9

TE Internal #: 66507-9

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Connector Contacts



Contact Type: **Pin**

Contact Size: **20**

Contact Base Material: **Brass**

Contact Mating Area Plating Material: **Gold**

Termination Method to Wire & Cable: **Crimp**

Features

Product Type Features

Product Type	Contact
Grade	Standard
Connector System	Cable-to-Cable
Connector & Contact Terminates To	Wire & Cable

Contact Features

	30 μ m
Pin Diameter	1.02 mm[.04 in]
Contact Type	Pin
Contact Size	20
Contact Base Material	Brass
Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	1.2 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Contact Retention in Housing	Crimp Snap-In
------------------------------	---------------

Wire Insulation Support	With
-------------------------	------

Dimensions

	.04 in
--	--------

Post Diameter	2.16 mm
---------------	---------

Accepts Wire Insulation Diameter Range	.76 – 1.02 mm [.03 – .04 in]
----------------------------------------	------------------------------

Wire Size	.08 – .2 mm ²
-----------	--------------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

For Use With	AMPLIMITE HDP-20, CPC Connectors
--------------	----------------------------------

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	1000
--------------------	------

Packaging Method	Loose Piece
------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
-----------------------------------------------	-----------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
----------------------------------------	------------------------------------------------------------------------------------------------

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	-------------------------------------------------------------------------------------

Solder Process Capability	Not applicable for solder process capability
---------------------------	----------------------------------------------

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous

materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Circular Power Connectors
(10)



Insertion & Extraction Tools
(2)



Portable Crimp Tools(4)

Customers Also Bought



TE Part #5748676-2
DIE CAST CBL CLMP KIT,
SZ 2



TE Part #5748676-3
DIE CAST CBL CLMP KIT,
SZ 3



TE Part #207464-2
CRIMP SNAP PLUG ASSY,
SZ 3



TE Part #205204-4
CRIMP SNAP PLUG ASSY,
SIZE 1



TE Part #66504-9
SOCKET CONTACT, 20 DF



TE Part #205206-3
CRIMP SNAP PLUG ASSY,
SIZE 2



TE Part #66505-9
SOCKET CONTACT, 20 DF



TE Part #66506-9
PIN CONTACT, 20 DF

Documents

[Product Drawings](#)
[PIN CONTACT, 20 DF](#)

English

[CAD Files](#)

[3D PDF](#)

[3D](#)

[Customer View Model](#)



[ENG_CVM_CVM_66507-9_CE_c-66507-9-ce.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_66507-9_CE_c-66507-9-ce.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_66507-9_CE_c-66507-9-ce.3d_stp.zip](#)

English

Datasheets & Catalog Pages

Signal Contacts

English

AMP Circular Connectors for Commercial Signal & Power Applications

English

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

Product Specifications

Application Specification

English

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English