


IoT OPTIMIZED LOW PROFILE QUARTZ CRYSTAL



2.5 x 2.0 x 0.6mm

RoHS/RoHS II Compliant

MSL = N/A: NOT APPLICABLE

ABM10W SERIES

FEATURES

- Optimized for energy saving wearables and IoT applications
- Plated at exceptionally low plating capacitance, as low as 4pF, with optimized ESR
- 0.6 mm max height ideally suited for height constrained designs
- Seam sealed for longterm reliability


APPLICATIONS

- Wearables
- Internet of Things (IoT)
- Bluetooth/Bluetooth Low Energy (BLE)
- Wireless modules
- Machine-to-machine (M2M) connectivity
- Ultra-low power MCU
- Near Field Communication (NFC)
- ISM Band

STANDARD SPECIFICATIONS

Parameters	Minimum	Typical	Maximum	Units	Notes
Frequency Range	16.0000		50.0000	MHz	
Operation Mode	Fundamental				
Operating Temperature Range	-40		+125	°C	See options
Storage Temperature	-55		+125	°C	
Frequency Tolerance @ +25°C	-10		+10	ppm	See options
Frequency Stability over the Operating Temperature (ref. to +25°C)	-10		+10	ppm	See options
Equivalent series resistance "R1" (over Operating Temperature Range) (CL=4pF)		< 70	100	Ω	16.0000 – 19.9999MHz
		< 50	80		20.0000 – 29.9999MHz
		< 40	60		30.0000 – 39.9999MHz
		< 25	40		40.0000 – 50.0000MHz
Equivalent series resistance "R1" (over Operating Temperature Range) (CL=6pF, 7pF, 8pF)		< 50	70	Ω	16.0000 – 19.9999MHz
		< 35	50		20.0000 – 29.9999MHz
		< 30	40		30.0000 – 39.9999MHz
		< 25	30		40.0000 – 50.0000MHz
Shunt capacitance (C0)		< 1.0	2.0	pF	
Load capacitance (CL)		4.0		pF	See options
Drive Level		10	100	μW	
Aging (1 year)	-2		+2	ppm	@ 25°C±3°C
Insulation Resistance	500			MΩ	@ 100Vdc ± 15V

IoT OPTIMIZED LOW PROFILE QUARTZ CRYSTAL



2.5 x 2.0 x 0.6mm




RoHS/RoHS II Compliant

MSL = N/A: NOT APPLICABLE

ABM10W SERIES

OPTIONS AND PART IDENTIFICATION (NOTE 1)

Note 1: Contact Abracon for part number requests with carrier frequency callouts up to 5 & 6 digit accuracy after the decimal.



IoT OPTIMIZED LOW PROFILE QUARTZ CRYSTAL



ABM10W SERIES



2.5 x 2.0 x 0.6mm





RoHS/RoHS II Compliant

MSL = N/A: NOT APPLICABLE

TYPICAL FREQUENCY Vs. TEMPERATURE CHARACTERISTICS



TYPICAL ESR (EQUIVALENT SERIES RESISTANCE) Vs. TEMPERATURE CHARACTERISTICS



(*) Plating Load = Load Capacitance (CL)




5101 Hidden Creek Ln Spicewood TX 78669
 Phone: 512-371-6159 | Fax: 512-351-8858
 For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 10.06.2020

ABRACON IS
 ISO9001-2015
 CERTIFIED

IoT OPTIMIZED LOW PROFILE QUARTZ CRYSTAL



ABM10W SERIES


2.5 x 2.0 x 0.6mm






RoHS/RoHS II Compliant

MSL = N/A: NOT APPLICABLE


TYPICAL FREQUENCY TOLERANCE DISTRIBUTION (AT 25°C ± 3°C)



TYPICAL ESR DISTRIBUTION (AT 25°C ± 3°C)



IoT OPTIMIZED LOW PROFILE QUARTZ CRYSTAL



ABM10W SERIES


2.5 x 2.0 x 0.6mm



RoHS/RoHS II Compliant





MSL = N/A: NOT APPLICABLE

SPICE MODELS (BASED ON TYPICAL VALUES AT 25°C ± 3°C)



Frequency: 16.0000MHz Plating Load: 4pF				Frequency: 16.0000MHz Plating Load: 6pF			
C0	=	0.65	pF	C0	=	0.65	pF
R1	=	22.77	Ω	R1	=	21.43	Ω
L1	=	70.34	mH	L1	=	70.13	mH
C1	=	1.41	fF	C1	=	1.41	fF
Frequency: 27.0000MHz Plating Load: 4pF				Frequency: 27.0000MHz Plating Load: 6pF			
C0	=	0.65	pF	C0	=	0.66	pF
R1	=	14.39	Ω	R1	=	17.38	Ω
L1	=	16.51	mH	L1	=	16.56	mH
C1	=	2.11	fF	C1	=	2.10	fF
Frequency: 50.0000MHz Plating Load: 4pF				Frequency: 50.0000MHz Plating Load: 6pF			
C0	=	0.89	pF	C0	=	0.87	pF
R1	=	8.40	Ω	R1	=	8.03	Ω
L1	=	3.24	mH	L1	=	3.19	mH
C1	=	3.13	fF	C1	=	3.18	fF

MECHANICAL DIMENSIONS




DIMENSIONS: mm

DIMENSIONS: mm

Note:

Due to material availability the Chamfer could be located on pin #1, 2 or 4. Be advised that the Chamfer location has no impact on the electrical performance of the device.

IoT OPTIMIZED LOW PROFILE QUARTZ CRYSTAL



ABM10W SERIES


2.5 x 2.0 x 0.6mm



RoHS/RoHS II Compliant

MSL = N/A: NOT APPLICABLE


REFLOW PROFILE



Zone	Description	Temperature	Time
1	Preheat	$T_{SMIN} \sim T_{SMAX}$ 150°C ~ 180°C	60 ~ 120 sec.
2	Reflow	T_L 217°C	45 ~ 90 sec.
3	Peak Heat	T_P 260°C MAX	10 sec.

PACKAGING

T3: Tape and reel (3,000 pcs/reel)



DIMENSIONS:mm



5101 Hidden Creek Ln Spicewood TX 78669
 Phone: 512-371-6159 | Fax: 512-351-8858
 For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 10.06.2020

ABRACON IS
 ISO9001-2015
 CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ABM10W-24.0000MHZ-4-D1X-T3](#) [ABM10W-30.0000MHZ-6-D1X-T3](#) [ABM10W-19.2000MHZ-7-D1X-T3](#) [ABM10W-22.5792MHZ-8-D1X-T3](#) [ABM10W-24.0000MHZ-7-D1X-T3](#) [ABM10W-26.0000MHZ-7-B1U-T3](#) [ABM10W-16.0000MHZ-8-J1Z-T3](#) [ABM10W-30.0000MHZ-8-B1U-T3](#) [ABM10W-38.4000MHZ-7-B1U-T3](#) [ABM10W-24.5760MHZ-6-D1X-T3](#) [ABM10W-24.0000MHZ-7-B1U-T3](#) [ABM10W-32.0000MHZ-7-D1X-T3](#) [ABM10W-48.0000MHZ-4-B1U-T3](#) [ABM10W-19.2000MHZ-8-D1X-T3](#) [ABM10W-25.0000MHZ-7-K1Z-T3](#) [ABM10W-16.3676MHZ-8-K1Z-T3](#) [ABM10W-24.0000MHZ-8-K1Z-T3](#) [ABM10W-32.0000MHZ-4-B1U-T3](#) [ABM10W-48.0000MHZ-8-B1U-T3](#) [ABM10W-16.0000MHZ-6-K1Z-T3](#) [ABM10W-30.0000MHZ-6-B1U-T3](#) [ABM10W-27.1200MHZ-4-D1X-T3](#) [ABM10W-16.0000MHZ-8-D1X-T3](#) [ABM10W-26.0000MHZ-8-K2Z-T3](#) [ABM10W-27.0000MHZ-8-D1X-T3](#) [ABM10W-16.0000MHZ-4-D2X-T3](#) [ABM10W-20.0000MHZ-8-K2Z-T3](#) [ABM10W-27.0000MHZ-8-B1U-T3](#) [ABM10W-50.0000MHZ-4-B1U-T3](#) [ABM10W-30.0000MHZ-4-B1U-T3](#) [ABM10W-20.0000MHZ-8-D1X-T3](#) [ABM10W-32.0000MHZ-8-D1X-T3](#) [ABM10W-50.0000MHZ-4-D1X-T3](#) [ABM10W-25.0000MHZ-6-K1Z-T3](#) [ABM10W-27.0000MHZ-6-K1Z-T3](#) [ABM10W-26.0000MHZ-6-B1U-T3](#) [ABM10W-27.1200MHZ-8-D1X-T3](#) [ABM10W-25.0000MHZ-8-K1Z-T3](#) [ABM10W-38.4000MHZ-6-B1U-T3](#) [ABM10W-22.0000MHZ-4-B1U-T3](#) [ABM10W-40.0000MHZ-4-B1U-T3](#) [ABM10W-25.0000MHZ-7-B2U-T3](#) [ABM10W-27.1200MHZ-7-D1X-T3](#) [ABM10W-24.5760MHZ-8-D1X-T3](#) [ABM10W-19.7079MHZ-4-D2X-T3](#) [ABM10W-20.0000MHZ-6-K1Z-T3](#) [ABM10W-25.0000MHZ-8-D1X-T3](#) [ABM10W-20.0000MHZ-4-D1X-T3](#) [ABM10W-38.4000MHZ-7-D1X-T3](#) [ABM10W-48.0000MHZ-7-K1Z-T3](#) [ABM10W-27.0000MHZ-4-B1U-T3](#) [ABM10W-48.0000MHZ-8-D1X-T3](#) [ABM10W-27.0000MHZ-6-D1X-T3](#) [ABM10W-27.0000MHZ-7-B1U-T3](#) [ABM10W-24.5760MHZ-8-B1U-T3](#) [ABM10W-25.0000MHZ-6-D1X-T3](#) [ABM10W-20.0000MHZ-4-B1U-T3](#) [ABM10W-24.0000MHZ-6-D1X-T3](#) [ABM10W-24.0000MHZ-6-D2X-T3](#) [ABM10W-27.0000MHZ-8-K1Z-T3](#) [ABM10W-16.0000MHZ-8-K1Z-T3](#) [ABM10W-19.2000MHZ-4-D1X-T3](#) [ABM10W-16.0000MHZ-4-B1U-T3](#) [ABM10W-16.0000MHZ-8-D2X-T3](#) [ABM10W-32.0000MHZ-8-B1U-T3](#) [ABM10W-24.0000MHZ-8-D2X-T3](#) [ABM10W-25.0000MHZ-4-K1Z-T3](#) [ABM10W-50.0000MHZ-8-B1U-T3](#) [ABM10W-24.5760MHZ-7-D1X-T3](#) [ABM10W-24.0000MHZ-8-D1X-T3](#) [ABM10W-27.1200MHZ-7-B1U-T3](#) [ABM10W-20.0000MHZ-8-K1Z-T3](#) [ABM10W-27.1200MHZ-6-D1X-T3](#) [ABM10W-24.5760MHZ-4-D1X-T3](#) [ABM10W-27.0000MHZ-4-D1X-T3](#) [ABM10W-24.0000MHZ-8-B1U-T3](#) [ABM10W-27.1200MHZ-7-K1Z-T3](#) [ABM10W-25.0000MHZ-8-D2X-T3](#) [ABM10W-24.3050MHZ-8-D1X-T3](#) [ABM10W-20.0000MHZ-8-B2U-T3](#) [ABM10W-24.0000MHZ-4-K1Z-T3](#) [ABM10W-40.0000MHZ-7-B1U-T3](#) [ABM10W-25.0000MHZ-8-B1U-T3](#) [ABM10W-22.1184MHZ-4-B2U-T3](#) [ABM10W-26.0000MHZ-4-B1U-T3](#) [ABM10W-16.0000MHZ-6-D1X-T3](#) [ABM10W-27.0000MHZ-6-B1U-T3](#) [ABM10W-24.3050MHZ-8-J1Z-T3](#) [ABM10W-39.0000MHZ-8-B1U-T3](#) [ABM10W-18.4320MHZ-4-D1X-T3](#) [ABM10W-48.0000MHZ-6-D1X-T3](#) [ABM10W-32.0000MHZ-4-D1X-T3](#) [ABM10W-40.0000MHZ-7-D1X-T3](#) [ABM10W-26.0000MHZ-7-D1X-T3](#) [ABM10W-40.0000MHZ-8-D1X-T3](#) [ABM10W-22.5792MHZ-7-B1U-T3](#) [ABM10W-25.0000MHZ-](#)

[6-B1U-T3](#) [ABM10W-26.0000MHZ-4-D1X-T3](#) [ABM10W-19.2000MHZ-8-D2X-T3](#) [ABM10W-40.0000MHZ-8-B1U-T3](#)