


High Performance Schottky Rectifier, 240 A





HAL	F-PA	K ([0-67)

PRIMARY CHARACTERISTICS				
I _{F(AV)}	240 A			
V_{R}	100 V			
Package	HALF-PAK (D-67)			
Circuit configuration	Single diode			

FEATURES

- 175 °C T_J operation
- · Low forward voltage drop



- · High frequency operation
- Guard ring for enhanced ruggedness and long term reliability
- · Designed and qualified for industrial level
- UL approved file E222165
- · Material categorization: for definitions of compliance please see www.vishav.com/doc?99912

DESCRIPTION

The VS-243NQ.. high current Schottky rectifier module series has been optimized for low reverse leakage at high temperature. The proprietary barrier technology allows for reliable operation up to 175 °C junction temperature. Typical applications are in high current switching power supplies, plating power supplies, UPS systems, converters, freewheeling diodes, welding, and reverse battery protection.

MAJOR RATINGS AND CHARACTERISTICS					
SYMBOL	CHARACTERISTICS	CHARACTERISTICS VALUES			
I _{F(AV)}	Rectangular waveform	240	А		
V _{RRM}		100	V		
I _{FSM}	$t_p = 5 \mu s sine$	25 500	А		
V _F	240 A _{pk} , T _J = 125 °C	0.72	V		
TJ	Range	-55 to +175	°C		

VOLTAGE RATINGS				
PARAMETER	SYMBOL	VS-243NQ100PbF	UNITS	
Maximum DC reverse voltage	V_{R}	V _R 100		
Maximum working peak reverse voltage	V_{RWM}	100	V	

ABSOLUTE MAXIMUM RATINGS					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum average forward current See fig. 5	I _{F(AV)}	50 % duty cycle at T _C = 132 °C, rectangular waveform 24		240	
Maximum peak one cycle non-repetitive surge current	I	5 µs sine or 3 µs rect. pulse	Following any rated load condition and with	25 500	Α
See fig. 7	IFSM	10 ms sine or 6 ms rect. pulse	rated V _{RRM} applied	3300	
Non-repetitive avalanche energy	E _{AS}	T _J = 25 °C, I _{AS} = 5.5 A, L = 1 mH		15	mJ
Repetitive avalanche current	I _{AR}	Current decaying linearly to zero in 1 μ s Frequency limited by T _J maximum V _A = 1.5 x V _R typical		1	Α



ELECTRICAL SPECIFICATIONS					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
	V _{FM} ⁽¹⁾	240 A	- T _J = 25 °C	0.95	V
Maximum forward voltage drop		480 A		1.26	
See fig. 1		240 A	T _J = 125 °C	0.72	
		480 A		0.85	
Maximum reverse leakage current	um reverse leakage current		V _B = Rated V _B	6	mA
See fig. 2	I _{RM}	T _J = 125 °C	v _R = nateu v _R	80	IIIA
Maximum junction capacitance	C _T	$V_R = 5 V_{DC}$ (test signal range 100 kHz to 1 MHz) 25 °C		5500	pF
Typical series inductance	L _S	From top of terminal hole to mounting plane		5.0	nH
Maximum voltage rate of change	dV/dt	Rated V _R		10 000	V/µs

Note

 $^{^{(1)}}$ Pulse width = 500 μ s

THERMAL - MECHANICAL SPECIFICATIONS						
PARAMETER		SYMBOL	TEST CONDITIONS	VALUES	UNITS	
Maximum junction and storage temperature range		T _J , T _{Stg}		-55 to +175	°C	
Maximum thermal resistance, junction to case		R _{thJC}	DC operation See fig. 4	0.19	°C/W	
Typical thermal resistance, case to heatsink		R _{thCS}	Mounting surface, smooth and greased	0.05		
Approximate weight				30	g	
				1.06	oz.	
minimum				3 (26.5)		
Mounting torque	maximum		Non-lubricated threads	4 (35.4)	$N \cdot m$ (lbf \cdot in)	
Tourisation	minimum		Non-lubricated tilleads	3.4 (30)		
Terminal torque	maximum			5 (44.2)		
Case style				HALF-PA	K module	




Fig. 1 - Maximum Forward Voltage Drop Characteristics




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics





Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current



I_{F(AV)} - Average Forward Current (A)

Fig. 6 - Forward Power Loss Characteristics




Fig. 7 - Maximum Non-Repetitive Surge Current





Fig. 8 - Unclamped Inductive Test Circuit

Note

 $\begin{array}{ll} \text{(1)} \ \ \text{Formula used: } T_C = T_J - (Pd + Pd_{REV}) \times R_{thJC}; \\ Pd = \text{forward power loss} = I_{F(AV)} \times V_{FM} \text{ at } (I_{F(AV)}/D) \text{ (see fig. 6)}; \\ Pd_{REV} = \text{inverse power loss} = V_{R1} \times I_R \text{ (1 - D); } I_R \text{ at } V_{R1} = \text{rated } V_R \\ \end{array}$

ORDERING INFORMATION TABLE

Device code



- Vishay Semiconductors product
- 2 Average current rating (x 10)
- 3 Product silicon identification
- 4 N = not isolated
- Q = Schottky rectifier diode
- 6 Voltage rating (100 = 100 V)
- 7 Lead (Pb)-free

LINKS TO RELATED DOCUMENTS				
Dimensions	www.vishay.com/doc?95020			



D-67 HALF-PAK

DIMENSIONS in millimeters (inches)









Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.