

MEMS CLOCK OSCILLATOR

ASDM



ASDM

RoHS/RoHS II Compliant

Life Size

2.5 x 2.0 x 0.85 mm

FEATURES:

- Low Power Consumption
- Exceptional Stability Over Temp. at -40°C to +85°C
- Low Cost-Compact QFN Plastic Packaging
- Compact Package design

APPLICATIONS:

- CCD Clock for VTR Camera
- Equipment Connected to PCs
- Low Profile Equipment
- Lower Cost Crystal Oscillator Replacement
- Computers and Peripherals
- Portable Electronics (MP3 Players, Games)
- Consumer Electronics such as TV's, DVR's, etc.
- Vibrant, Shock-Prone & Humid Environments for Industrial Equipment
- Demanding Military & Automotive Electronics

STANDARD SPECIFICATIONS:

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range:		1.0	-----	150	MHz	
Operating Temperature:		0	-----	+70	°C	See options
Storage Temperature:		-55	-----	+150	°C	
Supply Voltage (Vdd):		+1.8 ~ +3.3			V	See options
Supply Current (no load):	1.0 to 39.9999MHz	-----	7	15	mA	Vdd=3.3V No load RL=∞ T=25°C
	40.0 to 79.9999MHz	-----	8	15		
	80.0 to 124.9999MHz	-----	9	15		
	125.0 to 150MHz	-----	10	15		
Output Voltage:	V _{OH}	0.8*V _{dd}	-----	-----	V	15pF
	V _{OL}	-----	-----	0.2*V _{dd}		
Rise Time:	Tr	-----	1.3	3.0	ns	15pF; T=25°C 20%/80%*VDD
Fall Time:	Tf	-----	1.3	3.0		
Output Load:		15pF max / 10kΩ min.			pF	See options
Symmetry:		45	-----	55	%	@1/2Vdd
Startup Time:		-----	1.5	3.0	ms	
Disable Time:		-----	20	100	ns	
Disable Stand-by Current:		-----	-----	15	uA	
Tri-state Function (Stand-by) :		"1" (VIH≥0.75*Vdd) or Open: Oscillation "0" (VIH<0.25*Vdd) : Hi Z			V	
Cycle to cycle jitter:		-----	60	-----	ps	F=100MHz
Aging:		-5.0	-----	+5.0	ppm	First year

Absolute Maximum Ratings

Item	Minimum	Maximum	Unit	Condition
Supply Voltage	-0.3	+4.0	V	
Input Voltage	-0.3	Vdd+0.3	V	
Junction Temp.	-----	+150	°C	
Soldering Temp.	-----	+260	°C	40sec max
ESD			V	
HBM		2,000		
MM		200		
CDM		500		

REVISED: 1.4.2021

ABRACON IS
ISO9001-2015
CERTIFIED




5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit: www.abracon.com



OPTIONS AND PART IDENTIFICATION:


Programmed Orders (Quantity > 1,000pcs)



* For Quick turn-around programmable orders < 1000pcs: Due to the immediate availability of stock and the qty of the order, the parts may be delivered as BULK: Cut Tape, Loose parts in Antistatic Bag or in Tube(s). The MOQ per the series will still apply for Tube packaging.

Un-Programmed Orders (Quantity < 1,000pcs)

Blank un-programmed oscillators are available for quick turn engineering requirements. Please call ABRACON for more information



MEMS CLOCK OSCILLATOR

ASDM



ASDM

Pb | RoHS/RoHS II Compliant

Life Size

2.5 x 2.0 x 0.80 mm

OUTLINE DRAWING:

Recommended Land Pattern

Note: Recommend using an approximately 0.01uF bypass capacitor between PIN 2 and 4.

Dimension : mm (Inches)

No	Pin Terminal
1	Standby
2	GND
3	Output
4	VDD

TAPE & REEL: Tape and reel 1,000pcs/reel

FEEDING (PULL) DIRECTION

Tube: 140 ncs/tube

Unit orientation in tube:

Dimension : Inches (mm)

REFLOW PROFILE:

Ramp-Up Rate (200°C to Peak Temp)	3°C/Sec Max.
Preheat Time 150°C to 200°C	60-180 Sec
Time maintained above 217°C	60-150 Sec
Peak Temperature	255-260°C
Time within 5°C of actual Peak	20-40 Sec
Ramp-Down Rate	6°C/Sec Max.
Time 25°C to Peak Temperature	8 min Max.

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ASDM1-27.000MHZ-LC-T](#) [ASDM1-24.576MHZ-LC-T](#) [ASDM1-12.000MHZ-LC-T](#) [ASDM1-29.4912MHZ-LC-T](#) [ASDM1-80.000MHZ-LC-T](#) [ASDM1-60.000MHZ-LC-T](#) [ASDM1-25.000MHZ-LC-T](#) [ASDM1-10.000MHZ-LC-T](#) [ASDM1-4.000MHZ-LC-T](#) [ASDM1-33.000MHZ-LC-T](#) [ASDM1-33.333MHZ-LC-T](#) [ASDM1-11.0592MHZ-LC-T](#) [ASDM1-7.3728MHZ-LC-T](#) [ASDM1-24.000MHZ-LC-T](#) [ASDM1-16.000MHZ-LC-T](#) [ASDM1-30.000MHZ-LC-T](#) [ASDM1-14.7456MHZ-LC-T](#) [ASDM1-1.8432MHZ-LC-T](#) [ASDM1-8.000MHZ-LC-T](#) [ASDM1-48.000MHZ-LC-T](#) [ASDM1-100.000MHZ-LC-T](#) [ASDM1-44.000MHZ-LC-T](#) [ASDM1-50.000MHZ-LC-T](#) [ASDM1-14.31818MHZ-LC-T](#) [ASDM1-32.000MHZ-LC-T](#) [ASDM1-20.000MHZ-LC-T](#) [ASDM1-18.432MHZ-LC-T](#) [ASDM1-60.000MHZ-LR-T](#) [ASEM1-40.000MHZ-LC-T](#) [ASDM4-26.000MHZ-LR](#) [ASDM4-26.000MHZ-LR-T](#) [ASDM1-12.288MHZ-LC-T](#) [ASDM1-40.000MHZ-LC-T](#) [ASDM1-25.0000MHZ-LC-T](#)