

# 3.3V HCMOS/ TTL COMPATIBLE SMD CRYSTAL CLOCK OSCILLATOR



5.0 x 3.2 x 1.3mm

**ASFL1**



## FEATURES:

- Tri state function
- Suitable for high density SMT
- Available tight stability option +/-20ppm
- Seam sealed package assures high reliability performance
- Suitable for RoHS compliant reflow process

## APPLICATIONS:

- CCD clock for VTR camera
- Equipment connected to PC or PC cards
- Thin equipment
- Wireless communication
- PDA, Laptop computer

## STANDARD SPECIFICATIONS:

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range		0.321	-----	133.33	MHz	
Operating Temperature		-10	-----	+70	°C	See options
Storage Temperature		-55	-----	+125	°C	
Overall Frequency Stability		-100	-----	+100	ppm	See options
Supply Voltage (Vdd)		2.97	3.3	3.63	V	
Input Current	0.321MHz ~ 29.9MHz	-----	8	15	mA	
	30MHz ~ 79.9MHz	-----	20	45		
	80MHz ~ 133.33MHz	-----	28	85		
Symmetry (@ 1/2Vdd)		40	50	60	%	See options
Rise and Fall Time (Tr/Tf)	0.321MHz ~ 29.9MHz	-----	5	10	ns	
	30MHz ~ 79.9MHz	-----	5	7		
	80MHz ~ 133.33MHz	-----	3	7		
Output Load		-----	-----	15	pF	
		-----	-----	5	TTL	
Output Voltage	VOH	0.9*Vdd	-----	-----	V	
	VOL	-----	-----	0.1*Vdd	V	
Tri-state Function	VIH	0.7*Vdd	-----	-----	V	"1" or Open: Oscillation
	VIL	-----	-----	0.3*Vdd	V	"0": Output disable (Hi Z)
Disable Current		-----	-----	10	µA	
Start-up Time	0.321MHz ~ 29.9MHz	-----	1	10	ms	
	30MHz ~ 79.9MHz	-----	3	10		
	80MHz ~ 133.33MHz	-----	3	10		
Phase Jitter RMS (12kHz to 20MHz)		-----	-----	1	ps	Reference only. Please contact Abracon for specific frequencies
Aging		-5.0	-----	+5.0	ppm	@+25°C First year

## OPTIONS AND PART IDENTIFICATION:

(Left blank if standard)

ASFL1-  MHz -    -

Frequency in MHz
e.g. 24.576MHz
14.31818MHz
26.000MHz

Operating Temp.
I: 0°C ~ +50°C
D: -10°C ~ +60°C
E: -20°C ~ +70°C
F: -30°C ~ +70°C
N: -30°C ~ +85°C
L: -40°C ~ +85°C

Freq. Stability
J: ± 20 ppm(*)
R: ± 25 ppm
K: ± 30 ppm
H: ± 35 ppm
B: ± 40ppm
C: ± 50 ppm

Symmetry
Blank: 40/60% @1/2Vdd
S: 45/55% @1/2Vdd

(\*) Temp option I, D, E and -10°C ~ +70°C only.

Packaging
Blank: Bulk
T: 1000pcs/reel
T2: 250pcs/reel

ABRACON IS  
ISO9001:2008  
CERTIFIED



Visit [www.abracon.com](http://www.abracon.com) for Terms & Conditions of Sale **Revised: 04.13.11**  
30332 Esperanza, Rancho Santa Margarita, California 92688  
tel 949-546-8000 | fax 949-546-8001 | [www.abracon.com](http://www.abracon.com)

# 3.3V HCMOS /TTL COMPATIBLE SMD CRYSTAL CLOCK OSCILLATOR




5.0 x 3.2 x 1.3mm


ASFL1



## OUTLINE DRAWING:



Dimensions: inches (mm)




Pin	Function
1	Tri-State
2	GND
3	Output
4	Vdd

Note: Recommend using an approximately 0.01 $\mu\text{F}$  bypass capacitor between PIN 2 and 4.


## TAPE & REEL:

T= Tape and reel (1,000pcs/reel)  
T2= Tape and reel (250pcs/reel)

Dimensions: mm



## REFLOW PROFILE:



**ATTENTION:** Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS  
ISO9001:2008  
CERTIFIED



Visit [www.abracon.com](http://www.abracon.com) for Terms & Conditions of Sale **Revised: 04.13.11**  
30332 Esperanza, Rancho Santa Margarita, California 92688  
tel 949-546-8000 | fax 949-546-8001 | [www.abracon.com](http://www.abracon.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## ABRACON:

[ASFL1-14.31818MHZ-EK-T](#) [ASFL1-4.000MHZ-EK-T](#) [ASFL1-16.000MHZ-EK-T](#) [ASFL1-32.000MHZ-EK-T](#) [ASFL1-12.000MHZ-EK-T](#) [ASFL1-11.0592MHZ-EK-T](#) [ASFL1-8.000MHZ-EK-T](#) [ASFL1-48.000MHZ-EK-T](#) [ASFL1-33.333MHZ-EK-T](#) [ASFL1-25.000MHZ-EK-T](#) [ASFL1-3.6864MHZ-EK-T](#) [ASFL1-10.000MHZ-EK-T](#) [ASFL1-40.000MHZ-EK-T](#) [ASFL1-24.576MHZ-EK-T](#) [ASFL1-20.000MHZ-EK-T](#) [ASFL1-50.000MHZ-EK-T](#) [ASFL1-30.000MHZ-EK-T](#) [ASFL1-27.000MHZ-EK-T](#) [ASFL1-18.432MHZ-EK-T](#) [ASFL1-1.8432MHZ-EK-T](#) [ASFL1-14.7456MHZ-EK-T](#) [ASFL1-24.000MHZ-EK-T](#) [ASFL1-33.000MHZ-EK-T](#) [ASFL1-7.3728MHZ-EK-T](#) [ASFL1-1.8432MHZ-L-T](#) [ASFL1-10.000MHZ-L-T](#) [ASFL1-100.000MHZ-L-T](#) [ASFL1-11.0592MHZ-L-T](#) [ASFL1-12.000MHZ-L-T](#) [ASFL1-12.288MHZ-L-T](#) [ASFL1-14.31818MHZ-L-T](#) [ASFL1-14.7456MHZ-L-T](#) [ASFL1-16.000MHZ-L-T](#) [ASFL1-16.384MHZ-L-T](#) [ASFL1-18.432MHZ-L-T](#) [ASFL1-20.000MHZ-L-T](#) [ASFL1-24.000MHZ-L-T](#) [ASFL1-24.576MHZ-L-T](#) [ASFL1-25.000MHZ-L-T](#) [ASFL1-27.000MHZ-L-T](#) [ASFL1-29.4912MHZ-L-T](#) [ASFL1-3.6864MHZ-L-T](#) [ASFL1-30.000MHZ-L-T](#) [ASFL1-32.000MHZ-L-T](#) [ASFL1-32.768MHZ-L-T](#) [ASFL1-33.333MHZ-L-T](#) [ASFL1-4.000MHZ-L-T](#) [ASFL1-40.000MHZ-L-T](#) [ASFL1-48.000MHZ-L-T](#) [ASFL1-50.000MHZ-L-T](#) [ASFL1-60.000MHZ-L-T](#) [ASFL1-64.000MHZ-L-T](#) [ASFL1-66.666MHZ-L-T](#) [ASFL1-7.3728MHZ-L-T](#) [ASFL1-75.000MHZ-L-T](#) [ASFL1-8.000MHZ-L-T](#) [ASFL1-80.000MHZ-L-T](#) [ASFL1-32.768MHZ-EK-T](#) [ASFL1-64.000MHZ-EK-T](#) [ASFL1-10.000MHZ-EC-T](#) [ASFL1-100.000MHZ-EC-T](#) [ASFL1-12.000MHZ-EC-T](#) [ASFL1-12.288MHZ-EC-T](#) [ASFL1-125.000MHZ-EC-T](#) [ASFL1-133.330MHZ-EC-T](#) [ASFL1-14.31818MHZ-EC-T](#) [ASFL1-14.7456MHZ-EC-T](#) [ASFL1-16.000MHZ-EC-T](#) [ASFL1-16.384MHZ-EC-T](#) [ASFL1-18.432MHZ-EC-T](#) [ASFL1-20.000MHZ-EC-T](#) [ASFL1-24.000MHZ-EC-T](#) [ASFL1-24.576MHZ-EC-T](#) [ASFL1-25.000MHZ-EC-T](#) [ASFL1-27.000MHZ-EC-T](#) [ASFL1-29.4912MHZ-EC-T](#) [ASFL1-3.6864MHZ-EC-T](#) [ASFL1-30.000MHZ-EC-T](#) [ASFL1-32.000MHZ-EC-T](#) [ASFL1-32.768MHZ-EC-T](#) [ASFL1-33.333MHZ-EC-T](#) [ASFL1-4.000MHZ-EC-T](#) [ASFL1-40.000MHZ-EC-T](#) [ASFL1-48.000MHZ-EC-T](#) [ASFL1-50.000MHZ-EC-T](#) [ASFL1-60.000MHZ-EC-T](#) [ASFL1-64.000MHZ-EC-T](#) [ASFL1-66.666MHZ-EC-T](#) [ASFL1-7.3728MHZ-EC-T](#) [ASFL1-75.000MHZ-EC-T](#) [ASFL1-8.000MHZ-EC-T](#) [ASFL1-80.000MHZ-EC-T](#) [ASFL1-50.000MHz-ER-T](#) [ASFL1-28.63636MHZ-EC-T](#) [ASFL1-6.000MHZ-EC-T](#) [ASFL1-24.000MHZ-ER-T](#) [ASFL1-26.000MHZ-L-T](#) [ASFL1-12.000MHZ-ERS-T](#) [ASFL1-14.7456MHZ-LC-T](#) [ASFL1-12.288MHZ-LCS-T](#)