



NOTE :
- MARKING "A" is used to identify "STANDARD" terminal
- CRIMPING SPECIFICATION ACCORDING TO CS-64322-001

2	BOX TERMINAL	STAINLESS STEEL thickness=0.15 mm
1	BODY TERMINAL	high conductivity copper alloy thickness=0.2 mm
MARK	DESIGNATION	MATERIAL

0643221029	Sn	Sn		0.75	2.5	2.4	0.6	3.3	2.8	0.75	0.119
0643221219	Au 1.27μ MINI	Sn	Ni								
0643221039	Sn	Sn		0.50	2.3	2.2	0.6	3.1	2.6	0.75	0.117
0643221239	Au 1.27μ MINI	Sn	Ni								
0643221019	Sn	Sn		0.22 TO 0.44	2.0	1.7	0.6	3.1	2.6	0.75	0.112
0643221229	Au 1.27μ MINI	Sn	Ni								
PART NUMBER	CONTACT AREA	CRIMPING AREA	UNDERLAYER	CRIMPING RANGE (mm2)	A±0.2	B±0.2	rC ±0.15 -0.1	D±0.2	E±0.2	rF±0.1	WEIGHT (g)

(SKC) COTES CARACTERISTIQUES SPECIALES
INDICATION DIMENSIONS S.P.C DENOTES S.P.C DIMENSIONS
INDICATION DIMENSIONS CRITIQUES DENOTES CRITICAL DIMENSIONS
INDICATION DIMENSIONS FONCTIONNELLES DENOTES FUNCTIONAL DIMENSIONS
QUANTITE PAR FEUILLE INDIVIDUELLE
QUANTITY PER INDIVIDUAL SHEET

Revised Dwg EC NO: GZ008-0440 DRAWN BY: JIUOU CHKD BY: FPARLARI APPROVAL: LKLEIR	2008/05/19 2008/05/19 2008/05/19	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	FIRST ANGLE PROJECTION	
		mm	INCH	MM ONLY	MM ONLY	20:1	METRIC	CP RCPT TRM 0.6	
4 PLACES ±	---	±	---	DRAWN BY	DATE	TITLE			
3 PLACES ±	---	±	---	FPARLARI	2007/09/17	CP RCPT TRM 0.6			
2 PLACES ±	0.10	±	---	CHECKED BY	DATE				
1 PLACE ±	0.1	±	---	IDUCLOS	2007/09/17				
ANGULAR ± 2°				APPROVED BY	DATE				
				LSTICKEIR	2007/09/17				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		MATERIAL NO.		MOLEX INCORPORATED		SHEET NO.	
				A1		SD-64322-001		1 OF 1	