



Fuse-link, LV, 16 A, AC 660 V, DC 460 V, BS88/A2, 22 x 86 mm, gL/gG, BS

Catalog No. TIA16

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	16
Rated voltage			AC 660 V DC 460 V
Construction size			BS88/A2
Size			22 x 86 mm
Utilization category			gL/gG
Breaking Capacity		kA	80
usable for size/applications			general industrial applications
Standard/Approval			BS
Shape			offset bolted tags
Standards/Regulations			BS88-2 IEC 60269-2
Optional accessories			fuse-holder CM32F and RS32

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	16
Rated voltage		V	660
Voltage type			AC/DC
Rated switching capacity		kA	80
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No

Additional product information (links)

Product datasheet (pdf)	http://www1.cooperbusssmann.com/pdf/0bed7fd6-7dbd-4d9c-a937-9d817ce5c100.pdf
-------------------------	---