

# **IRWIN TOOLS.**

## **T6TON6VS workshop vice.**



### **Workshop Vice – medium duty range.**

This compact bench vice with anvil is specifically designed for medium-duty workshop applications for both, the professional craftsman and the DIY enthusiast who expect a compact vice with superior clamping force, safety features and excellent finish.

Strong and durable, the body and sliding jaw are cast from close grained grey iron which is machined on all friction surfaces for a smooth reliable action.

The jaws, handle and main screw are steel.

The main screw has a two-start rolled acme thread to speed the jaws from fully closed to fully open with a minimum of winding.

<b>Item No.</b>	<b>T6TON6VS</b>
<b>Weight.</b>	22.25kg.
<b>Jaw width.</b>	152mm.
<b>Throat depth (from top of jaw to top of slide).</b>	75mm.
<b>Max. jaw opening.</b>	145mm.
<b>Overall length of vice when closed.</b>	385mm
<b>Overall height of vice.</b>	212mm.
<b>Distance between centres of front fixing-holes.</b>	203mm
<b>Distance from mid-point between front fixing-hole centres to centre of rear fixing-hole.</b>	176mm
<b>Fixing-hole diameter.</b>	14.5mm
<b>Swivel-base casting thickness in fixing-hole area.</b>	14.5mm