

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0877131001](#)

Status: **Active**

Overview: [Serial ATA Connectors and Cable Assemblies](#)

Description: 1.27mm Pitch Serial ATA Host Receptacle, Surface Mount, Vertical, Standard Height, with 3.70mm Plastic Locating Peg, 0.76µm Gold (Au) Selective Plating, 22 Circuits, Lead-Free

Documents:


[3D Model](#)

[Drawing \(PDF\)](#)

[Product Specification PS-87713-016-001 \(PDF\)](#)

[Packaging Specification PK-87713-100 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)



Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Receptacles
Series	87713
Application	Board-to-Board, Signal
Comments	3.70mm Plastic Locating Peg
Overview	Serial ATA Connectors and Cable Assemblies
Product Name	Serial ATA
UPC	822348699360

Physical

(p)ower-(s)ignal Configuration	15p - 7s
Circuits (Loaded)	22
Circuits (maximum)	22
Durability (mating cycles max)	500
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.467/g
Number of Rows	1
Orientation	Vertical
PCB Locator	Yes
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V

Solder Process Data

Duration at Max. Process Temperature (seconds)	010
--	-----

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[87713 Series](#)

Mates With

[87679](#) , [87799](#) , [87703](#)

Lead-free Process Capability
Max. Cycles at Max. Process Temperature
Process Temperature max. C

REFLOW
001
260

Material Info

Reference - Drawing Numbers

Electrical Model Document

EE-78178-001, EE-78328-001, EE-78328-002,
EE-87703-003, EE-87713-001

Packaging Specification

PK-87713-100

Product Specification

PS-87713-016-001

S-Parameter Model

SP-87713-001

Sales Drawing

SD-87713-001

This document was generated on 01/21/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION