


# ED130F-XXP

PCB Terminal Blocks > PCB Connector-Plug

Date:2018-12-26Version:1.1





The web catalog is for reference only. Dinkle remains the right of product modification and engineering change of the design.

The final product is made according to engineering drawing.

#### **Product Description**

Pitch: 5.00 mm, 300V, 7A

#### General information

Short description	PCB Connector Plug , Wire protector type
Category	PCB Connector Plug
Pitch (mm)	5.00
Color	Blue(default)
Connection method	Wire protector type
Type of locking	Without
Length (mm)	5.00xP
Width (mm)	13.50
Height (mm)	10.80
Number of positions	02~03
Level	Single level

#### Material information

Insulation material	High-temperature plastics
Insulation material group	IIIa
Flame retardant rating , compliant with UL94	V0



Conductor material	Copper Alloy	
Plating of conductor surface	Tinned	
Connection data-IEC		
Rated current (A)	12	
Rated voltage (II/2)(V)	400	
Rated voltage (III/2) (V)	320	
Rated voltage (III/3)(V)	250	
Rated impulse voltage (II/2)(KV)	4	
Rated impulse voltage (III/2)(KV)	4	
Rated impulse voltage (III/3)(KV)	4	
Conductor cross section solid. min (mm²)	0.5	
Conductor cross section solid.max (mm²)	1.5	
Conductor cross section stranded. min (mm²)	0.5	
Conductor cross section stranded. max (mm²)	1.5	
Conductor cross section flexible, with min ferrule without plastic sleeve (mm²)	0.34	
Conductor cross section flexible, with max ferrule without plastic sleeve (mm²)	1	
Conductor cross section flexible, with min ferrule with plastic sleeve (mm²)	0.34	
Conductor cross section flexible, with max ferrule with plastic sleeve (mm²)	1	
2 conductors with same cross section, solid, max (mm²)	1	
2 conductors with same cross section, stranded, max (mm²)	1	
2 conductors with same cross section flexible, with min ferrule without plastic sleeve (mm²)	0.25	
2 conductors with same cross section flexible, with max ferrule without plastic sleeve (mm²)	0.34	
2 conductors with same cross section flexible, min twin ferrules with plastic sleeve (mm²)	0.5	
2 conductors with same cross section flexible, max twin ferrules with plastic sleeve (mm²)	0.5	
Screw thread	M2.5	
Slotted screwdriver size (Blade thickness x Width)(mm)	0.6x3.5	
Philips screwdriver size	PH1	
Rated torque (N.m)	0.3	
Stripping Length (mm)	5~6	



### Connection data-UL

300
7
300
7
22
14
22
14

### **Environment & Safety**

Finger protection (YES or NO)	YES
Operating temperature. max (°C)	130
Operating temperature. min (°C)	-40

### **UL** Recognized


Wire Range (Group B)(AWG)	22~14
Rated voltage (Group B)(V)	300
Rated current (Group B)(A)	7
Wire Range (Group D)(AWG)	22~14
Rated voltage (Group D)(V)	300
Rated current (Group D)(A)	7

# **CUL** Recognized

Wire Range (Group B)(AWG)	22~14
Rated voltage (Group B)(V)	300
Rated current (Group B)(A)	7
Wire Ranget (Group D)(AWG)	22~14
Rated voltage (Group D)(V)	300
Rated current (Group D)(A)	7

# Drawings





# Approvals





