Polymer Blowguns

The Parker Legris polymer blowgun offers **ease of use**, **energy saving**, adaptability and efficiency. These blowguns comply with **international regulations** for health, **safety** and **noise** levels.

Product Advantages

Quality & Performance	Comply with international standards for noise and pressure regulation	
	Powerful flow with progressive control	
	Rotating nozzle for directional jet	
	Durable, shock-resistant materials	Glegus .
	100% leak and flow-tested in production	
	Date coding to guarantee quality and traceability	
Safety &	40% energy consumption reduction with Energy-Saving model	
Sustainable	Complete user safety with the Safety model	🕶 🛛 🗄 🗉
Development	Wide selection of nozzles which comply with noise and	
	pressure level regulations	Manufacturing Workshops
Ergonomics &	Comfortable to use	Cleaning
Versatility	Lightweight and easy to use	Mixing
	Wide range of models and nozzles for optimum blowing power and flow rate	Ejection
	Lower or upper connection	Packaging

Applications

Technical Characteristics

Compatible Fluids	Compressed air Other fluids: contact us	Component Materials	
Working Pressure	0 to 10 bar	Nozzle: • aluminium (Standard blowgun) • nickel-plated brass (Safety and other blowguns) Body:	
Working Temperature	Air: -15°C to +50°C Dry air: -20°C to +80°C		
Tubes	Recoil tubes and hose		
	-		
Regulations		Trigger: technical polymer	
Compliance for all blowguns: DI: 97/23/EC (PED) DI: 2002/95/EC (BoHS)	Compliance for specific blowguns:	Connection: nickel-plated brass	

DI: 97/23/EC (PED) DI: 2002/95/EC (RoHS), 2011/65/EC DI: 1907/2006 (REACH)

Protection of design All designs and models of Parker Legris blowguns have been registered with the following numbers: 13224 / 13225 / 13226.

Iegris

7-6

Di. 1910.242 (b) [OSI A]
The static pressure must be less than 30 psi in case the nozzle becomes blocked.
DI: 1910.95 (b) [OSHA]
The noise level must be less than 90 dBA over 8 hours' exposure.
DI: 2003/10/EC
Regulation relating to exposure to noise, particularly with regard to risks to hearing. The noise level must be less than 87 dBA.

Silicone-free