## Standard tin snips



- For continuous, straight and curved cuts
- With no opening stop and with extra pointed cutter head
- Edges with micro-serrations for slip-proof working
- Particularly robust, for unusually challenging situations: Snips completely tempered and burnished.
  Cutter inductively hardened
- PVC dipped handles
- Available in right or left cutting versions
- On carded hang pack



## Shape and straight cutting snips, without opening stop

Nº	←a→		←b→		max.	å	4	Ø	
	mm	"	mm	"	mm		kg	qty.	V5
D216-280-B-SBSK	280	11	34	1 3/8	1,0	+ +	0.58	5	
D216-280L-B-SBSK	280	11	34	1 3/8	1,0	++	0.58	5	



YouTube ►



- For long continuous and straight cuts
- Extra long blade is ideal for cutting through metal sheets
- D218 Painted handles
- D118 PVC dipped handles
- Available as right cutter (in 300 mm dimension also available as left cutter)

## **Pelican snips**



