
Fibccom


G510 GSM/GPRS Module

Perfect Wireless Experience



G510 is a wireless module with LCC package and supports 850/900/ 1800/1900MHz. It is extremely small in size, has low power consumption and powerful EMC and ESD performance, and has an Internal TCP/IP protocol stack and two serial ports, providing perfect voice call function and high speed data transmission for customers.

G510 module is ideal for today's wireless payment, telematics, hand held devices and industrial IoT applications.



Available For

Global Market

Fibocom

G510 GSM/GPRS Module

Perfect Wireless Experience

G510 GSM/GPRS Module Technical Specifications

Product Features

- Quad Band: 850/900/1800/1900MHz
- Dimensions: 20.2 x 22.2 x 2.5mm
- LCC 42pin
- •Weight: 2.5 gram
- Operating Temperature: -40 ~ +85°C
- Operating Voltage: 3.3 ~ 4.5V
- Current Consumption:
 1.0mA@sleep mode (DRX9)

- TX Power: 850/900MHz class 4 (2W) 1800/1900MHz class 1 (1W)
- RX Sensitivity: -109dBm (850/900MHz)
- -108dBm (1800/1900MHz)
- AT Command Set:FIBOCOM proprietary AT commands/ GSM 07.05/GSM 07.07/GSM 07.10

- Data
- Embedded TCP/UDP
- GPRS: Multi-slot class 10 (4 Down; 2 Up; 5 Total) Max Downlink 85.6 Kbps Coding Scheme CS1-CS4SMS
- MUX: Basic Mode MO/MT Text and PDU modes Cell broadcast
 SMS: MO/MT Text and PDU modes Cell broadcast

Interfaces

- SIM Card:1.8V/2.8V
- UART: BR from 2400 to 460800
- Power on/off
- UART X 2
- Analog Audio X 2

Highlights

- OpenCPU
- Watchdog inside
- Jamming Detection
- LBS



Approvals

SRRC/CCC/NAL/CE/GCF/ROHS/ANATEL

Copyright © 1999~2015 Fibocom Wireless Inc. | Subject to changes in technology, design and availability | E-mail : market@fibocom.com | Tel : +86 755-2673 3555