

The Gigadevice Starter Kits include an I/O Extension Header for all of the package pins to allow quick connection of prototyping and probing. Also included on all of the boards is the GD-Link, a programmer and debugger for the GD32 MCU's.

The Gigadevice Evaluation Boards allow full evaluation of the on-chip peripherals, including connectivity, and also feature external memories and display. The GD-Link is also include on all of the boards.

## Starter Kits available

GD32103B-START (GD32F103VBT6)

GD32103C-START (GD32F103VCT6)

GD32130C-START (GD32F130C8T6)

GD32130G-START (GD32F130G8U6)

GD32150C-START (GD32F150C8T6)

GD32150G-START (GD32F150G8U6)

GD32170C-START (GD32F170C8T6)

## About Gigadevice

Established in 2005. Headquartered in Beijing, China.

A fabless semiconductor company focused on advanced Non-Volatile Memory and 32-bit ARM Cortex Microcontroller solutions.

Complete product portfolio of Serial Flash Memory including SPI NOR, SPI NAND.

Wide range of 32-bit MCU product lines targeting various application segments.

Strong R&D resource and capability specialized in NVM and MCU development.

Dominating Serial Flash Memory and 32-bit MCU market in China with largest customer base.

First domestic memory supplier to complete an IPO on the Shanghai Stock Exchange.

GigaDevice Semiconductor Europe Ltd  
Innovation House  
Molly Millars Close  
Wokingham  
Berkshire  
UK  
RG41 2RX

Website: <http://us.gigadevice.com>

Email: [info.EMEA@gigadevice.com](mailto:info.EMEA@gigadevice.com)

## Part Number

## Board Features




GD32103B-EVAL

GD32F103VBT6 MCU, User Led's, Push Button, 2 USART's, SmartCard Function, POT, Buzzer, 2Kb EERPOM, 4Mb SPI NOR Flash, 8Mbit SRAM, Micro SD Card Interface, USB, CAN, 3.2" TFT LCD (320x240)




GD32103C-EVAL

GD32F103VCT6 MCU, User LED's, Push Button, 2 USART's, POT, Headphone Socket, 2Kb EEPROM, 4Mb SPI NOR Flash, USB, CAN, Micro SD Card Interface, 1GB NAND Flash, 3.2" TFT LCD (320x240)



GD32103E-EVAL

GD32F103ZET6 MCU, User LED's, Push Button, 2 USART's, POT, Headphone Socket, 2Kb EEPROM, 4Mb SPI NOR Flash, USB, CAN, Micro SD Card Interface, 1GB NAND Flash, 3.2" TFT LCD (320x240)




GD32105C-EVAL

GD32F105VCT6 MCU, User LED's, Push Botton, 2 USART's, POT, Headphone Socket, 2Kb EEPROM, 4Mb SPI NOR Flash, USB, CAN, 1GB NAND Flash, 3.2" TFT LCD (320x240)




GD32107C-EVAL

GD32F107VCT6 MCU, User LED's, Push Button's, 2 USART's, POT, Headphone Socket, 2Kb EEPROM, 4Mb SPI NOR Flash, USB, CAN, 1GB NAND Flash, 10/100 Ethernet, 3.2" TFT LCD (320x240)




GD32150R-EVAL

GD32150R8T6 MCU, User LED's, Push Buttons, USART, RS-485, POT, Headphone Socket, 2Kb EEPROM, USB, HDM-CEC, Touch Interface, IrDA, Buzzer, 2.2" TFT Display




GD32190R-EVAL

GD32F190R8T6 MCU, User LED's, 2 USART's, POT, Headphone Socket, 2Kb EEPROM, 4Mb SPI NOR Flash, Op-AMP, CAN, Touch Interface, IrDA, LCD



GD32207C-EVAL

GD32F207VCT6 MCU, User LED's, Push Buttons, USART, POT, 2Kb EEPROM, 16Mbit SPI NOR Flash, USB, CAN, 1GB NAND Flash, 10/100 Ethernet, Micro SD Card Interface, 3.5" RGB-LCD (320x480)



GD32207I-EVAL

GD32F207IXT6 MCU, User LED's, Push Buttons, USART, POT, 2Kb EEPROM, 16Mbit SPI NOR Flash, USB, CAN, 1GB NAND Flash, 10/100 Ethernet, Micro SD Card Interface, Headphone Socket, 256Mbit SDRAM, VGA Camera, 4.3" RGB (480x272)