


DCO SD2 MD 24 (917 941)


- Space-saving terminal block with integrated surge protection
- Disconnection module for isolating signal circuits for maintenance work
- For installation in conformity with the lightning protection zones concept at the boundaries from $0_B - 2$ and higher



Figure without obligation



Basic circuit diagram DCO SD2 MD 24



Dimension drawing DCO RK MD 24

Energy-coordinated two-stage arrester with disconnection function that has no leakage current to earth protects one unearthed pair as well as balanced interfaces.

Type Part No.	DCO SD2 MD 24 917 941
SPD class	TYPE 2 Pt
Nominal voltage (U_N)	24 V
Max. continuous operating d.c. voltage (U_C)	33 V
Max. continuous operating a.c. voltage (U_C)	23 V
Nominal current at 80 °C (I_N)	0.5 A
C2 Total nominal discharge current (8/20 μ s) (I_n)	10 kA
C2 Nominal discharge current (8/20 μ s) per line (I_n)	5 kA
Voltage protection level line-line for I_n C2 (U_p)	≤ 50 V
Voltage protection level line-PG for I_n C2 (U_p)	≤ 750 V
Voltage protection level line-line at 1 kV/ μ s C3 (U_p)	≤ 45 V
Voltage protection level line-PG at 1 kV/ μ s C3 (U_p)	≤ 650 V
Series resistance per line	1.8 ohms
Cut-off frequency line-PG (f_c)	6 MHz
Capacitance line-line (C)	≤ 1.0 nF
Capacitance line-PG (C)	≤ 6 pF
Operating temperature range	-40°C...+80°C
Degree of protection	IP 00
For mounting on	35 mm DIN rails acc. to EN 60715
Connection (input/output)	spring / spring
Cross-sectional area (solid)	0.34 - 2.5 mm ²
Cross-sectional area (flexible)	0.34 - 2.5 mm ²
Earthing via	DIN rail / terminal
Enclosure material	polyamide PA 6.6
Colour	yellow
Test standards	IEC 61643-21 / EN 61643-21
Extended technical data:	-----
- Max. discharge current (8/20) [1/2 - PG], [1+2 - PG] (I_{max})	20 kA
- Voltage protection level line-PG at 1 kV/ μ s C3 after being subjected to I_{max} (U_p)	≤ 650 V
Weight	31 g
Customs tariff number	85363010
GTIN	4013364150607
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.