



## 40 V, 2 A low drop power Schottky rectifier





#### **Features**

- Very small conduction losses
- Negligible switching losses
- · Low forward voltage drop
- · Surface mount miniature package
- Avalanche rated
- ECOPACK2 component

#### **Applications**

- Telecom power supply
- · Set-top box power supply
- TV power supply
- · Battery charger

#### **Description**

lectronics sales office

Single chip Schottky rectifiers designed for high frequency miniature switched mode power supplies such as adaptors and on board DC/DC converters.

Packaged in SMB, SMA Flat, SMA Flat Notch and SMB Flat, the STPS2L40 is ideal for surface mounting and used in low voltage, high frequency inverters, free wheeling and polarity protection applications.

Product status
STPS2L40

Product summary				
Symbol	Value			
I <sub>F(AV)</sub>	2 A			
V <sub>RRM</sub>	40 V			
T <sub>j(max.)</sub>	150 °C			
V <sub>F(typ.)</sub>	0.31 V			



### **Characteristics**

Table 1. Absolute ratings (limiting values at 25 °C, unless otherwise specified)

Symbol	Parameter	arameter			
V <sub>RRM</sub>	Repetitive peak reverse voltage	Repetitive peak reverse voltage			
		SMB	T <sub>L</sub> = 130 °C		
$I_{F(AV)}$	Average forward current, $\delta$ = 0.5, square wave	SMB Flat	T <sub>L</sub> = 140 °C	2	Α
		SMA Flat, SMA Flat Notch	T <sub>L</sub> = 130 °C		
I <sub>FSM</sub>	Surge non repetitive forward current	t <sub>p</sub> = 10 ms sinusoidal	75	Α	
P <sub>ARM</sub>	Repetitive peak avalanche power $t_p$ = 10 $\mu$ s, $T_j$ = 125 $^{\circ}$				W
T <sub>stg</sub>	Storage temperature range				°C
Tj	Maximum operating junction temperature <sup>(1)</sup>				°C

<sup>1.</sup>  $(dP_{tot}/dT_j) < (1/R_{th(j-a)})$  condition to avoid thermal runaway for a diode on its own heatsink.

Table 2. Thermal resistance parameter

Symbol	Parameter	Max. value	Unit		
	R <sub>th(j-l)</sub> Junction to lead	SMB	20		
D.		SMB Flat	10	°C/W	
►th(j-l)		SMA Flat	20	C/VV	
		SMA Flat Notch	20		

For more information, please refer to the following application note:

AN5088: Rectifiers thermal management, handling and mounting recommendations

Table 3. Static electrical characteristics

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
		T <sub>j</sub> = 25 °C		-		220	μA
I <sub>R</sub> <sup>(1)</sup>	I <sub>R</sub> <sup>(1)</sup> Reverse leakage current	T <sub>j</sub> = 100 °C	V <sub>R</sub> = 40 V	-		20	mA
		T <sub>j</sub> = 125 °C		-	38	80	mA
		T <sub>j</sub> = 25 °C	I <sub>F</sub> = 1 A	-		0.39	
		T <sub>j</sub> = 125 °C		-	0.25	0.28	
V <sub>F</sub> <sup>(1)</sup>	Forward voltage drop	T <sub>j</sub> = 25 °C		-		0.43	V
VF.	Torward voltage drop	T <sub>j</sub> = 125 °C	1F - Z /	-	0.31	0.34	v
		T <sub>j</sub> = 25 °C	I <sub>F</sub> = 4 A	-		0.50	
		T <sub>j</sub> = 125 °C	IF - 4 //	-	0.39	0.45	

<sup>1.</sup> Pulse test:  $t_p = 380 \ \mu s, \ \delta < 2\%$ 

To evaluate the conduction losses, use the following equation:

$$P = 0.22 \times I_{F(AV)} + 0.06 \times I_{F^{2}(RMS)}$$

DS2146 - Rev 6 page 2/17






For more information, please refer to the following application notes related to the power losses :


- AN604: Calculation of conduction losses in a power rectifier
- AN4021: Calculation of reverse losses on a power diode


DS2146 - Rev 6 page 3/17




#### 1.1 Characteristics (curves)









DS2146 - Rev 6 page 4/17



Figure 5. Normalized avalanche power derating versus pulse duration (T<sub>i</sub> = 125 °C)





Figure 6. Relative variation of thermal impedance junction to ambient versus pulse duration (SMB)



to lead versus pulse duration (SMB flat)




Figure 7. Relative variation of thermal impedance junction | Figure 8. Relative variation of thermal impedance junction to ambient versus pulse duration (SMA Flat)




Figure 9. Reverse leakage current versus reverse voltage applied (typical values)





Figure 10. Junction capacitance versus reverse voltage applied (typical values)



DS2146 - Rev 6 page 5/17



Figure 11. Forward voltage drop versus forward current (high level)




Figure 12. Forward voltage drop versus forward current (low level)




Figure 13. Thermal resistance junction to ambient versus copper surface under each lead (SMB)




Figure 14. Thermal resistance junction to ambient versus copper surface under each lead (SMB flat)





Figure 15. Thermal resistance junction to ambient versus copper surface under each lead (SMA Flat, SMA Flat Notch)



DS2146 - Rev 6 page 6/17

Downloaded from Arrow.com.




## 2 Package information


In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: <a href="https://www.st.com">www.st.com</a>. ECOPACK is an ST trademark.


### 2.1 SMB package information

- Epoxy meets UL94, V0
- · Lead-free package

Figure 16. SMB package outline








DS2146 - Rev 6 page 7/17



Table 4. SMB package mechanical data

	Dimensions					
Ref.	Millin	neters	Inches (for reference only)			
	Min.	Max.	Min.	Max.		
A1	1.90	2.45	0.074	0.097		
A2	0.05	0.20	0.001	0.008		
b	1.95	2.20	0.076	0.087		
С	0.15	0.40	0.005	0.016		
D	3.30	3.95	0.129	0.156		
E	5.10	5.60	0.200	0.221		
E1	4.05	4.60	0.159	0.182		
L	0.75	1.50	0.029	0.060		

Figure 17. SMB recommended footprint



DS2146 - Rev 6 page 8/17



## 2.2 SMB Flat package information

- Epoxy meets UL94, V0
- Lead-free package

Figure 18. SMB Flat package outline





Table 5. SMB Flat mechanical data

	Dimensions						
Ref.		Millimeters			Inches		
	Min.	Тур.	Max.	Min.	Тур.	Max.	
Α	0.90		1.10	0.035		0.044	
b	1.95		2.20	0.076		0.087	
С	0.15		0.40	0.005		0.016	
D	3.30		3.95	0.129		0.156	
Е	5.10		5.60	0.200		0.221	
E1	4.05		4.60	0.159		0.182	
L	0.75		1.50	0.029		0.060	
L1		0.40			0.016		
L2		0.60			0.024		

DS2146 - Rev 6 page 9/17



Figure 19. Footprint recommendations, dimensions in mm (inches)



DS2146 - Rev 6 page 10/17



## 2.3 SMA Flat package information

- Epoxy meets UL94, V0
- Lead-free package

Figure 20. SMA Flat package outline





Table 6. SMA Flat package mechanical data

	Dimensions					
Ref.	Millimeters			Inc	ches (for reference on	ly)
	Min.	Тур.	Max.	Min.	Тур.	Max.
А	0.90		1.10	0.035		0.044
b	1.25		1.65	0.049		0.065
С	0.15		0.40	0.005		0.016
D	2.25		2.95	0.088		0.117
Е	4.80		5.60	0.188		0.221
E1	3.95		4.60	0.155		0.182
L	0.75		1.50	0.029		0.060
L1		0.50			0.020	
L2		0.50			0.020	

DS2146 - Rev 6 page 11/17



Figure 21. SMA Flat recommended footprint in mm (inches)



DS2146 - Rev 6 page 12/17



## 2.4 SMA Flat Notch package information

- Epoxy meets UL94, V0
- Cooling method: by conduction (C)
- · Band indicates cathode

Figure 22. SMA Flat Notch package outline





Table 7. SMA Flat Notch package mechanical data

			Dime	nsions		
Ref.		Millimeters		Inches (for reference only)		
	Min.	Тур.	Max.	Min.	Тур.	Max.
A1	0.90		1.10	0.035		0.044
A1		0.05			0.002	
b	1.25		1.65	0.049		0.065
С	0.15		0.40	0.005		0.016
D	2.25		2.90	0.088		0.115
E	5.00		5.35	0.196		0.211
E1	3.95		4.60	0.155		0.182
G		2.00			0.079	
G1		0.85			0.033	
L	0.75		1.20	0.029		
L1		0.45			0.018	
L2		0.45			0.018	
L3		0.05			0.002	
V			8°			8°
V1			8°			8°

DS2146 - Rev 6 page 13/17



Figure 23. SMA Flat Notch recommended footprint in mm (inches)



DS2146 - Rev 6 page 14/17



# **3** Ordering information

**Table 8. Ordering information** 

Order code	Marking	Package	Weight	Base qty.	Delivery mode
STPS2L40U	GD4	SMB	0.107 g	2500	Tape and reel
STPS2L40UF	FGD4	SMB Flat	0.050 g	5000	Tape and reel
STPS2L40AF	F2L4	SMA Flat	0.035 g	10 000	Tape and reel
STPS2L40AFN	A24	SMA Flat Notch	0.039 g	10 000	Tape and reel

DS2146 - Rev 6 page 15/17



## **Revision history**

Table 9. Document revision history

Date	Version	Changes
Jul-2003	2A	Last update.
31-Jan-2007	3	Reformatted to current standard. Added ECOPACK statement. Added SMBflat package.
18-Sep-2008	4	Reformatted to current standard. Updated ECOPACK statement. Added SMAflat package.
04-Dec-2018	5	Updated Table 1. Absolute ratings (limiting values at 25 $^{\circ}$ C, unless otherwise specified) and Figure 5. Normalized avalanche power derating versus pulse duration (T <sub>j</sub> = 125 $^{\circ}$ C).
27-Sep-2019	6	Added Section 2.4 SMA Flat Notch package information.



#### IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to <a href="https://www.st.com/trademarks">www.st.com/trademarks</a>. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2019 STMicroelectronics - All rights reserved

DS2146 - Rev 6 page 17/17