

Absolute Maximum Ratings		Values		Units
Symbol	Conditions ¹⁾			
V _{CES}		1200		V
V _{CGR}	R _{GE} = 20 kΩ	1200		V
I _C	T _{case} = 25/80 °C	150 / 110		A
I _{CM}	T _{case} = 25/80 °C; t _p = 1 ms	300 / 220		A
V _{GES}		± 20		V
P _{tot}	per IGBT, T _{case} = 25 °C	830		W
T _j , (T _{stg})		- 40 ... +150 (125)		°C
V _{isol}	AC, 1 min.	2 500 ⁷⁾		V
humidity	DIN 40 040	Class F		
climate	DIN IEC 68 T.1	40/125/56		
Inverse Diode		FWD ⁶⁾		
I _F = - I _C	T _{case} = 25/80 °C	150 / 100	200 / 135	A
I _{FM} = - I _{CM}	T _{case} = 25/80 °C; t _p = 1 ms	300 / 220	300 / 220	A
I _{FSM}	t _p = 10 ms; sin.; T _j = 150 °C	1100	1450	A
I _t ²	t _p = 10 ms; T _j = 150 °C	6000	10500	A ² s


Characteristics		min.	typ.	max.	Units
Symbol	Conditions ¹⁾				
V _{(BR)CES}	V _{GE} = 0, I _C = 4 mA	≥ V _{CES}	-	-	V
V _{GE(th)}	V _{GE} = V _{CE} , I _C = 4 mA	4,5	5,5	6,5	V
I _{CES}	V _{GE} = 0 } T _j = 25 °C V _{CE} = V _{CES} } T _j = 125 °C	-	0,2	2	mA
		-	9	-	mA
I _{GES}	V _{GE} = 20 V, V _{CE} = 0	-	-	1	μA
V _{CEsat}	I _C = 100 A } V _{GE} = 15 V; I _C = 150 A } T _j = 25 (125) °C	-	2,5(3,1)	3(3,7)	V
V _{CEsat}	I _C = 150 A } T _j = 25 (125) °C	-	3(3,8)	-	V
g _{fs}	V _{CE} = 20 V, I _C = 100 A	54	-	-	S
C _{CHC}	per IGBT	-	-	700	pF
C _{ies}	V _{GE} = 0 V _{CE} = 25 V f = 1 MHz	-	6,5	8,5	nF
C _{oes}		-	1000	1500	pF
C _{res}		-	500	600	pF
L _{CE}		-	-	20	nH
t _{d(on)}	V _{CC} = 600 V V _{GE} = + 15 V; - 15 V ³⁾ I _C = 100 A, ind. load R _{Gon} = R _{Goff} = 6,8 Ω T _j = 125 °C	-	160	320	ns
t _r		-	80	160	ns
t _{d(off)}		-	400	520	ns
t _f		-	70	100	ns
E _{on} ⁵⁾		-	13	-	mWs
E _{off} ⁵⁾		-	11	-	mWs
Inverse Diode ⁸⁾					
V _F = V _{EC}	I _F = 100 A } V _{GE} = 0 V; I _F = 150 A } T _j = 25 (125) °C	-	2,0(1,8)	2,5	V
V _F = V _{EC}		-	2,25(2,1)	-	V
V _{TO}	T _j = 125 °C	-	-	1,2	V
r _T	T _j = 125 °C	-	8	11	mΩ
I _{RRM}	I _F = 100 A; T _j = 25 (125) °C ²⁾	-	35(50)	-	A
Q _{rr}	I _F = 100 A; T _j = 25 (125) °C ²⁾	-	5(14)	-	μC
FWD of types "GAL", "GAR" ⁸⁾					
V _F = V _{EC}	I _F = 100 A } V _{GE} = 0 V; I _F = 150 A } T _j = 25 (125) °C	-	1,85(1,6)	2,2	V
V _F = V _{EC}		-	2,0(1,8)	-	V
V _{TO}	T _j = 125 °C	-	-	1,2	V
r _T	T _j = 125 °C	-	5	7	mΩ
I _{RRM}	I _F = 100 A; T _j = 25 (125) °C ²⁾	-	40(65)	-	A
Q _{rr}	I _F = 100 A; T _j = 25 (125) °C ²⁾	-	5(15)	-	μC
Thermal Characteristics					
R _{thjc}	per IGBT	-	-	0,15	°C/W
R _{thjc}	per diode / FWD "GAL; GAR"	-	-	0,30/0,25	°C/W
R _{thch}	per module	-	-	0,038	°C/W

SEMITRANS® M IGBT Modules

SKM 150 GB 123 D
SKM 150 GAL 123 D ⁶⁾
SKM 150 GAR 123 D ⁶⁾



SEMITRANS 3



Features

- MOS input (voltage controlled)
- N channel, Homogeneous Si
- Low inductance case
- Very low tail current with low temperature dependence
- High short circuit capability, self limiting to 6 * I_{cnom}
- Latch-up free
- Fast & soft inverse CAL diodes⁸⁾
- Isolated copper baseplate using DCB Direct Copper Bonding Technology
- Large clearance (12 mm) and creepage distances (20 mm).

Typical Applications: → B 6-141

- Switching (not for linear use)

1) T_{case} = 25 °C, unless otherwise specified

2) I_F = - I_C, V_R = 600 V,

- di_F/dt = 1000 A/μs, V_{GE} = 0 V

3) Use V_{GEoff} = -5 ... -15 V

5) See fig. 2 + 3; R_{Goff} = 6,8 Ω

6) The free-wheeling diodes of the GAL and GAR types have the data of the inverse diodes of SKM 200 GB 123 D

7) V_{isol} = 4000 V_{rms} on request

8) CAL = Controlled Axial Lifetime Technology.

Cases and mech. data → B6-142 SEMITRANS 3




Fig. 1 Rated power dissipation $P_{tot} = f(T_C)$




Fig. 2 Turn-on /-off energy $= f(I_C)$




Fig. 3 Turn-on /-off energy $= f(R_G)$




Fig. 4 Maximum safe operating area (SOA) $I_C = f(V_{CE})$




Fig. 5 Turn-off safe operating area (RBSOA)





Fig. 6 Safe operating area at short circuit $I_C = f(V_{CE})$



$T_j = 150\text{ }^{\circ}C$
 $V_{GE} \geq 15\text{ V}$

Fig. 8 Rated current vs. temperature $I_C = f(T_C)$




Fig. 9 Typ. output characteristic, $t_p = 80\text{ }\mu s$; $25\text{ }^{\circ}C$




Fig. 10 Typ. output characteristic, $t_p = 80\text{ }\mu s$; $125\text{ }^{\circ}C$

$$P_{cond(t)} = V_{CEsat(t)} \cdot I_C(t)$$

$$V_{CEsat(t)} = V_{CE(TO)(T_j)} + r_{CE(T_j)} \cdot I_C(t)$$

$$V_{CE(TO)(T_j)} \leq 1,5 + 0,002 (T_j - 25) \text{ [V]}$$

$$\text{typ.: } r_{CE(T_j)} = 0,010 + 0,00004 (T_j - 25) \text{ } [\Omega]$$

$$\text{max.: } r_{CE(T_j)} = 0,015 + 0,00005 (T_j - 25) \text{ } [\Omega]$$

$$\text{valid for } V_{GE} = +15 \begin{matrix} +2 \\ -1 \end{matrix} \text{ [V]; } I_C > 0,3 I_{Cnom}$$

Fig. 11 Saturation characteristic (IGBT)
 Calculation elements and equations




Fig. 12 Typ. transfer characteristic, $t_p = 80\text{ }\mu s$; $V_{CE} = 20\text{ V}$






Fig. 13 Typ. gate charge characteristic

$I_{Cpuls} = 100 \text{ A}$




$V_{GE} = 0 \text{ V}$
 $f = 1 \text{ MHz}$

Fig. 14 Typ. capacitances vs. V_{CE}



$T_j = 125 \text{ }^\circ\text{C}$
 $V_{CE} = 600 \text{ V}$
 $V_{GE} = \pm 15 \text{ V}$
 $R_{Gon} = 6,8 \text{ } \Omega$
 $R_{Goff} = 6,8 \text{ } \Omega$
induct. load

Fig. 15 Typ. switching times vs. I_C



$T_j = 125 \text{ }^\circ\text{C}$
 $V_{CE} = 600 \text{ V}$
 $V_{GE} = \pm 15 \text{ V}$
 $I_C = 100 \text{ A}$
induct. load

Fig. 16 Typ. switching times vs. gate resistor R_G




Fig. 17 Typ. CAL diode forward characteristic




Fig. 18 Diode turn-off energy dissipation per pulse




Fig. 19 Transient thermal impedance of IGBT
 $Z_{thJC} = f(t_p)$; $D = t_p / t_c = t_p \cdot f$




Fig. 20 Transient thermal impedance of inverse CAL diodes
 $Z_{thJC} = f(t_p)$; $D = t_p / t_c = t_p \cdot f$




Fig. 22 Typ. CALdiode reverse recovery current $I_{RR} = f(I_F; R_G)$




Fig. 23 Typ. CAL diode reverse recovery current $I_{RR} = f(di_F/dt)$

Typical Applications include

- Switched mode power supplies
- DC servo and robot drives
- Inverters
- DC choppers (versions GAL and GAR)
- AC motor speed control
- Inductive heating
- UPS Uninterruptable power supplies
- General power switching applications
- Electronic (also portable) welders
- Pulse frequencies also above 15 kHz




Fig. 24 Typ. CAL diode recovered charge $Q_{rr} = f(di/dt)$

SEMITRANS 3

Case D 56




UL Recognized

File no. E 63 532

CASED56

SKM 150 GB 123 D

SKM 150 GB 173 D




Dimensions in mm

SKM 150 GAL 123 D

Case D 57 (→ D 56)


GCIGGAL



SKM 150 GAR 123 D

Case D 58 (→ D 56)

GCIGGAR



Case outline and circuit diagrams

Mechanical Data

Symbol	Conditions	Values			Units
		min.	typ.	max.	
M ₁	to heatsink, SI Units (M6)	3	—	5	Nm
	to heatsink, US Units	27	—	44	lb.in.
M ₂	for terminals, SI Units (M6)	2,5	—	5	Nm
	for terminals US Units	22	—	44	lb.in.
a		—	—	5x9,81	m/s ²
w		—	—	325	g

This is an electrostatic discharge sensitive device (ESDS). Please observe the international standard IEC 747-1, Chapter IX.

Three devices are supplied in one SEMIBOX B without mounting hardware, which can be ordered separately under Ident No. 33321100 (for 10 SEMITRANS 3). Larger packing units of 12 and 20 pieces are used if suitable

Accessories → B 6 - 4.
SEMIBOX → C - 1.

⁶⁾ Freewheeling diode → B 6 - 137, remark 6.