

Vectron International**Filter specification****TFS 70AW****1/5****Measurement condition**

Ambient temperature:	23	°C
Input power level:	0	dBm
Terminating impedance: *		
Input:	213 Ω	-64.3 pF
Output:	134 Ω	-83.2 pF

Characteristics

Remark:

The reference level for the relative attenuation a_{rel} of the TFS 70AW is the minimum of the pass band attenuation. This value is defined as the insertion loss a_e . The nominal frequency f_N is fixed at 70 MHz without any tolerance. The values of relative attenuation a_{rel} are guaranteed for the whole operating temperature range. The frequency shift of the filter in the operating temperature range is included in the production tolerance scheme.

D a t a		typ. value		tolerance / limit	
Insertion loss (reference level)		a_e	9.5 dB	max.	12 dB
Nominal frequency		f_N	-		70 MHz
Passband		PB	-	$f_N \pm$	1 MHz
Pass band ripple			0.4 dB	max.	1 dB
Relative attenuation		a_{rel}			
f_N	...	$f_N \pm$	1.0 MHz	0.4 dB	max. 1 dB
$f_N \pm$	1.0 MHz	...	$f_N \pm$	1.2 MHz	max. 3 dB
$f_N -$	10 MHz	...	$f_N -$	4 MHz	min. 40 dB
$f_N -$	4 MHz	...	$f_N -$	2.55 MHz	min. 25 dB
$f_N +$	2.55 MHz	...	$f_N +$	3 MHz	min. 25 dB
$f_N +$	3 MHz	...	$f_N +$	10 MHz	min. 40 dB
Group delay ripple within PB		p-p	75 ns	max.	200 ns
Phase linearity within PB		p-p	2.8 deg	max.	4.5 deg
Operating temperature range		OTR	-		- 55 °C ... + 85 °C
Storage temperature range			-		- 55 °C ... + 85 °C
Temperature coefficient of frequency		TC_f **	-18 ppm/K		

*) The terminating impedances depend on parasitics and q-values of matching elements and the board used, and are to be understood as reference values only. Should there be additional questions do not hesitate to ask for an application note or contact our design team.



***) $\Delta f(\text{Hz}) = TC_f(\text{ppm/K}) \times (T - T_0) \times f_{cat}(\text{MHz})$.

Generated:**Checked / Approved:**

Vectron International GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@vectron.com


Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Filter characteristic



Construction and pin connection

(All dimensions in mm)




1	Input
2	Input RF Return
3	Ground
4	Ground
5	Ground
6	Output
7	Output RF Return
8	Ground
9	Ground
10	Ground

Date code: Year + week

U	2006
V	2007
W	2008
...	

50 Ω Test circuit



Vectron International GmbH
 Potsdamer Straße 18
 D 14 513 TELTOW / Germany
 Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
 E-Mail: tft@vectron.com

Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Stability characteristics, reliability

After the following tests the filter shall meet the whole specification:

1. Shock: 500g, 1 ms, half sine wave, 3 shocks each plane;
DIN IEC 68 T2 - 27
2. Vibration: 10 Hz to 500 Hz, 0,35 mm or 5 g respectively, 1 octave per min, 10 cycles per plane, 3 planes;
DIN IEC 68 T2 - 6
3. Change of temperature: -55 °C to 125 °C / 30 min. each / 10 cycles
DIN IEC 68 part 2 – 14 Test N
4. Resistance to solder heat (reflow): reflow possible: three times max.;
for temperature conditions refer to the attached "Air reflow temperature conditions" on page 4;

This filter is RoHS compliant (2002/95/EG, 2005/618/EG)


Packing

Tape & Reel: IEC 286 – 3, with exception of value for N and minimum bending radius;
tape type II, embossed carrier tape with top cover tape on the upper side;

max. pieces of filters per reel:	2000
reel of empty components at start:	min. 300 mm
reel of empty components at start including leader:	min. 500 mm
trailer:	min. 300 mm


Tape (all dimensions in mm)

W	:16,00 ± 0,3
Po	:4,00 ± 0,1
Do	:1,50 +0,1/-0
E	:1,75 ± 0,10
F	:7,50 ± 0,10
G(min)	:0,60
P2	:2,00 ± 0,1
P1	:12,00 ± 0,1
D1(min)	:1,50 +0,1/-0
Ao	:7,60 ± 0,10
Bo	:9,60 ± 0,10
Ct	:13,5



Reel (all dimensions in mm)

A	:330
W1	:16,4
W2(max)	:22,4
N(min)	: 50
C	:13,0



The minimum bending radius is 45 mm.


Vectron International GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@vectron.com

Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Air reflow temperature conditions

Conditions	Exposure
Average ramp-up rate (30°C to 217°C)	less than 3°C/second
> 100°C	between 300 and 600 seconds
> 150°C	between 240 and 500 seconds
> 217°C	between 30 and 150 seconds
Peak temperature	max. 260°C
Time within 5°C of actual peak temperature	between 10 and 30 seconds
Cool-down rate (Peak to 50°C)	less than 6°C/second
Time from 30°C to Peak temperature	no greater than 300 seconds

Chip-mount air reflow profile



Vectron International GmbH
 Potsdamer Straße 18
 D 14 513 TELTOW / Germany
 Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
 E-Mail: tft@vectron.com

Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

History

Version	Reason of Changes	Name	Date
1.0	- Generation of development specification	Strehl	14.12.2005
1.1	- added 40 dB relative attenuation	Chilla	23.12.2005
1.2	- added 3 dB relative attenuation - added 25 dB relative attenuation	Chilla	07.02.2006
1.3	- operating temperature range extended	Pfeiffer	29.03.2006
1.4	- terminating impedances, typical values, filter characteristics and matching configuration added - passband ripple: limit changed to 1 dB	Pfeiffer	24.07.2006
2.0	- Extend lower OTR / STR as requested by customer from -45°C...+85°C to -55°C...+85°C	TCUK	28.03.2013