



**+** TERMINALS & SPLICES

AUTOMOTIVE, TRUCK, BUS, & OFF-ROAD TERMINALS



✓ Active

TE CONNECTIVITY (TE)

## 2.8MM RECP,SEAL,20AWG

1.5/2.8 Connector System , 2.8mm Connector System

1326032-2

TE Internal Number: 1326032-2

EU RoHS Compliant

EU ELV Compliant

**Terminal & Splice Style** Receptacle

**Mating Tab Width** 2.8 mm [.11 in]

**Mating Tab Thickness** .8 mm [.031 in]

**Terminal Transmits** 0 – 24 A (Low Power)

**Wire Size (AWG)** 20

[↓ PRODUCT DRAWING](#)  
English

[↓ 3D PDF](#)

### DOCUMENTATION

Product Drawings

#### 2.8mm RECEPTACLE, SEALED

PDF

English

CAD Files

#### 3D PDF

PDF

3D

#### Customer View Model

2D\_DXF.ZIP

English

### Customer View Model

3D\_IGS.ZIP

English

### Customer View Model

3D\_STP.ZIP

English

---

Product Specifications

Application Specification

### 2.8-Mm Terminal System (Sealed And Unsealed)

PDF

English

---

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

#### Product Type Features

**Sealable** Yes

**Receptacle Style** 180°

---

#### Body Features

**Seal Type** Single Wire Seal (SWS)

---

#### Contact Features

**Crimp Type** F-Crimp

**Typical Current Rating (A)** 10

**Terminal & Splice Style** Receptacle

**Mating Tab Width** 2.8 mm [ .11 in ]

**Mating Tab Thickness** .8 mm [ .031 in ]

**Interface Plating** Tin (Sn)

**Contact Termination Area Plating Material** Tin (Sn)

---

#### Termination Features

**Termination Method** Crimp

---

#### Dimensions

**Wire Size (AWG)** 20

**Wire Size (mm<sup>2</sup>)** .5

**Wire Size Search (AWG)** 20

**Wire Size Search (mm<sup>2</sup>)** .5

**Wire Insulation Diameter** 1.4 – 1.85 mm [ .055 – .073 in ]

---

Packaging Features

**Packaging Quantity** 3000

**Packaging Method** Package

---

Other

**Terminal Transmits** 0 – 24 A (Low Power)

---

**PRODUCT COMPLIANCE**



Statement of Compliance

**Statement of Compliance**

PDF

---