



Click [here](#) for the 3D model.

### General Information

Series	HHBC
Style	Through-Hole
Features	Noise Solution, Switching Power Supply Outlets, DC-DC Converter
RoHS	Yes
Miscellaneous	45 (K) Temperature Rise Max.
Core	Fe-Si

### Specifications

Inductance	97 uH
Inductance Tolerance	20%
Current	12 A
Temperature Range	-40/+125°C
DC Resistance	16 mOhms

### Dimensions

D	41.2mm MAX
T	20.3mm MAX
LL	9mm +/-3mm
S	14mm NOM
Wire Size	1.7mm

### Packaging Specifications

Packaging	Tray
Packaging Quantity	80
Component Weight	65 g