
# LaserRange-Master Gi5





## Laser distance meter – with green DLD laser technology



- Green laser technology
- Extremely bright green laser cross at front in the DLD design achieves high-quality lines as well as a clean and clear and therefore easily visible line image
- Point-precise measuring with laser to determine lengths exactly
- The area and volume functions permit the acquisition of room sizes, for example to calculate material quantities
- Min/Max continuous measurement
- Digital bubble level is used to align the measuring device
- Tilt sensor calibration
- 360° inclination sensor for determining the horizontal and vertical distance
- Measured value memory for 50 entries
- High measuring accuracy up to 50 m: ± 2 mm\*
- Inside measurement range: 0,05 m to 50 m
- 2 selectable measurement reference points: front and rear
- Illuminated 4-line colour LCD
- Sturdy, ergonomically designed, rubberised casing

#### **TECHNICAL DATA**

ACCURACY ± 2 mm (typical)\*

MEASUREMENT RANGE max. 50 m

MINIMAL RANGE 0,05 m

LASER Class 2 < 1mW

LASER WAVELENGTH 515 nm

**OPERATING CONDITIONS** -10°C

STORAGE CONDITIONS -20°C ... 70°C

**UNIT** (selectable) m / inch / ft

#### **AUTOMATIC SWITCH-OFF**

30 sec laser / 3 min device

#### **FUNCTIONS**

distances, areas, volumes, continuous measurement, angle function 1 + 2 + 3 \*\*, digital bubble level

#### POWER SUPPLY

Batteries 2 x 1,5 V type AA


**DIMENSIONS** (W x H x D) 50 x 122 x 27 mm

WEIGHT with batteries 140 g

- \* See operating instructions for specific accuracies
- \*\* In combination with 360° inclination senso



ARTICLE	ARTICLE NO	EAN-CODE	PU
LaserRange-Master Gi5	080.838A	4 021563 703722	5





### LaserRange-Master Gi5

inclusive softbag + batteries (2 x 1,5 V type AA)

Packaging dimension (W  $\times$  H  $\times$  D) 90 x 295 x 55 mm











