



Click [here](#) for the 3D model.

### Dimensions

D	32mm MAX
T	30mm MAX
H	24mm MAX
LL	5mm +/-2mm
S	10mm NOM
S1	25mm NOM
Wire Size	1.3mm

### Packaging Specifications

Packaging	Tray
Packaging Quantity	150
Component Weight	33 g

### General Information

Series	SCR22
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	65 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

### Specifications

Voltage AC	250 VAC
Inductance	1500 uH
Current	10 A
Temperature Range	-25/+120°C
DC Resistance	12 mOhms