


Low drop power Schottky rectifier

Datasheet - production data



Features

- Low forward voltage drop meaning very small conduction losses
- Low switching losses allowing high frequency operation
- Insulated package: TO-220FPAB
 - Insulating voltage = 2000 V_{RMS} sine
- Avalanche capability specified
- ECOPACK[®]2 compliant component for D²PAK on demand

Description

Dual center tap Schottky rectifiers designed for high frequency switched mode power supplies and DC to DC converters.

These devices are intended for use in low voltage, high frequency inverters, free-wheeling and polarity protection applications.

Table	1:	Device	summary
-------	----	--------	---------

Symbol	Value
I _{F(AV)}	2 x 10 A
Vrrm	45 V
V _F (typ.)	0.44 V
T _j (max.)	150 °C

October 2016

DocID8001 Rev 5

www.st.com

This is information on a product in full production.

1 Characteristics

Table 2: Absolute ratings (limiting values, per diode, at 25 °C, unless otherwise specified)

Symbol			Value	Unit			
Vrrm	Repetitive peak revers	e voltage			45	V	
I _{F(RMS)}	Forward rms current				30	А	
		TO-220AB /	Tc = 135 °C	Per diode	10		
	Average forward current δ = 0.5, square wave	•	-	Tc = 130 °C	Per device	20	^
IF(AV)		TO-220FPAB	T _C = 115 °C	Per diode	10	A	
		Tc = 100 °C		Per device	20		
IFSM	Surge non repetitive fo	180	А				
Parm	Repetitive peak avalar	285	W				
T _{stg}	Storage temperature ra		-65 to +150				
Tj	Maximum operating ju	nction temperatu	re ⁽¹⁾		150		

Notes:

 $^{(1)}(dP_{tot}/dT_j) < (1/R_{th(j-a)})$ condition to avoid thermal runaway for a diode on its own heatsink.

Table 3: Thermal parameters

Symbol	Paramete	Max. value	Unit		
			Per diode	4.5	
Duni	Junction to case	TO-220FPAB	Total	3.5	°C/W
R _{th(j-c)} J	Junction to case	TO-220AB D²PAK	Per diode	2.2	
			Total	1.3	
		TO-220FPAB		2.5	
Rth(c)	R _{th(c)} Coupling			0.3	

When the diodes 1 and 2 are used simultaneously:

 $\Delta T_{j \text{ (diode1)}} = P_{\text{(diode1)}} x R_{\text{th}(j-c)} \text{ (per diode)} + P_{\text{(diode2)}} x R_{\text{th}(c)}$





Characteristics

	I able 4: Static electrical characteristics (per diode)						
Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
I_ (1)	IR ⁽¹⁾ Reverse leakage current	Tj = 25 °C	$V_{R} = V_{RRM}$	-		0.2	mA
IR		Tj = 125 °C		-	65	130	
		Tj = 25 °C	I _F = 10 A	-		0.55	
VF ⁽¹⁾	Forward valtage drap	Tj = 125 °C			0.44	0.5	V
	Forward voltage drop	T _j = 25 °C	I⊧ = 20 A	-		0.73	v
		T _j = 125 °C	I⊧ = 20 A	-	0.62	0.72	

Table 4: Static electrical characteristics (per diode)

Notes:

 $^{(1)}\text{Pulse test:}$ tp = 380 µs, δ < 2%


To evaluate the conduction losses, use the following equation:


 $\mathsf{P} = 0.28 \ x \ \mathsf{I}_{\mathsf{F}(\mathsf{AV})} + 0.022 \ x \ \mathsf{I}_{\mathsf{F}^2(\mathsf{RMS})}$




Characteristics

STPS20L45C









4/15

DocID8001 Rev 5



Characteristics








In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: *www.st.com*. ECOPACK[®] is an ST trademark.

- Cooling method: by conduction (C)
- Epoxy meets UL 94,V0
- Recommended torque value: 0.55 N·m for TO-220AB
- Maximum torque value: 0.7 N·m for TO-220AB











STPS20L45C


Table 5: TO-220AB package mechanical data						
	Dimensions					
Ref.	Millime	eters	Inches			
	Min.	Max.	Min.	Max.		
А	4.40	4.60	0.173	0.181		
b	0.61	0.88	0.240	0.035		
b1	1.14	1.70	0.045	0.067		
С	0.48	0.70	0.019	0.028		
D	15.25	15.75	0.600	0.620		
D1	1.27 typ.		0.050 typ.			
E	10.00	10.40	0.394	0.409		
е	2.40	2.70	0.094	0.106		
e1	4.95	5.15	0.195	0.203		
F	1.23	1.32	0.048	0.052		
H1	6.20	6.60	0.244	0.260		
J1	2.40	2.72	0.094	0.107		
L	13.00	14.00	0.512	0.551		
L1	3.50	3.93	0.138	0.155		
L20	16.40 typ.		0.646 typ.			
L30	28.90 typ.		1.138	3 typ.		
θΡ	3.75	3.85	0.148	0.152		
Q	2.65	2.95	0.104	0.116		

8/15



2.2 TO-220FPAB package information

Figure 11: TO-220FPAB package outline





STPS20L45C


Table 6: TO-220FPAB package mechanical data							
		Dimensions					
Ref.	Millim	eters	Incl	nes			
	Min.	Max.	Min.	Max.			
A	4.40	4.60	0.173	0.181			
В	2.5	2.7	0.098	0.106			
D	2.5	2.75	0.098	0.108			
E	0.45	0.70	0.018	0.028			
F	0.75	1	0.030	0.039			
F1	1.15	1.70	0.045	0.067			
F2	1.15	1.70	0.045	0.067			
G	4.95	5.2	0.195	0.205			
G1	2.4	2.7	0.094	0.106			
н	10	10.4	0.394	0.409			
L2	16 ty	yp.	0.63	typ.			
L3	28.60	30.6	1.126	1.205			
L4	9.8	10.6	0.386	0.417			
L5	2.9	3.6	0.114	0.142			
L6	15.9	16.4	0.626	0.646			
L7	9	9.3	0.354	0.366			
Dia	3	3.2	0.118	0.126			

10/15

DocID8001 Rev 5



2.3 D²PAK package information





This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.




STPS20L45C

Table 7: D ² PAK package mechanical data					
Ref.	Millim	eters	Incl	hes	
	Min.	Max.	Min.	Max.	
A	4.36	4.60	0.172	0.181	
A1	0.00	0.25	0.000	0.010	
b	0.70	0.93	0.028	0.037	
b2	1.14	1.70	0.045	0.067	
С	0.38	0.69	0.015	0.027	
c2	1.19	1.36	0.047	0.053	
D	8.60	9.35	0.339	0.368	
D1	6.90	8.00	0.272	0.311	
D2	1.10	1.50	0.043	0.060	
E	10.00	10.55	0.394	0.415	
E1	8.10	8.90	0.319	0.346	
E2	6.85	7.25	0.266	0.282	
е	2.54	typ.	0.100		
e1	4.88	5.28	0.190	0.205	
н	15.00	15.85	0.591	0.624	
J1	2.49	2.90	0.097	0.112	
L	1.90	2.79	0.075	0.110	
L1	1.27	1.65	0.049	0.065	
L2	1.30	1.78	0.050	0.070	
R	0.4	typ.	0.015		
V2	0°	8°	0°	8°	

12/15







3 Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
STPS20L45CT	STPS20L45CT	TO-220AB	1.95 g	50	Tube
STPS20L45CFP	STPS20L45CFP	TO-220FPAB	1.7 g	50	Tube
STPS20L45CG-TR	STPS20L45CG	D ² PAK	1.38 g	1000	Tape and reel

Table 8: Ordering information

4 Revision history

Table 9: Document revision history

Date	Revision	Changes
Jul-2003	3C	Last release.
22-Mar-2007	4	Removed ISOWATT and TO-247 packages.
06-Oct-2016	5	Updated cover page. Updated Section 3: "Characteristics" and Section 3.1: "Characteristics (curves)" and Section 5: "Ordering information" and Section 4.4: "D ² PAK package information".



IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2016 STMicroelectronics - All rights reserved

