

# AI-TWIN 2X10 -14 RD - Ferrule

3201026

<https://www.phoenixcontact.com/us/products/3201026>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, sleeve length: 14 mm, color: red

## Your advantages

- These special ferrules allow chain bridges to be set up with ease
- The TWIN ferrules provide a practical way of crimping two conductors in one ferrule
- Different versions of the individual TWIN ferrules can be selected for specific applications

## Commercial data

Item number	3201026
Packing unit	1 pc
Minimum order quantity	100 pc
Sales key	BH34
Product key	BH3413
Catalog page	Page 486 (C-3-2019)
GTIN	4017918094577
Weight per piece (including packing)	0.956 g
Weight per piece (excluding packing)	0.956 g
Customs tariff number	85369010
Country of origin	DE

# AI-TWIN 2X10 -14 RD - Ferrule



3201026

<https://www.phoenixcontact.com/us/products/3201026>

## Technical data

### Product properties


Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M

### Connection data

#### Conductor connection

Conductor cross section flexible max.	10 mm <sup>2</sup>
Conductor cross section AWG max.	8
Stripping length	19 mm

### Dimensions

Dimensional drawing	
Sleeve length	14 mm
Maximum stripping length	19 mm
Ferrule diameter	6.5 mm
Sleeve wall thickness	0.2 mm
Insulating collar thickness	0.4 mm
Inner dimensions of the insulating collar	7.2 mm

### Material specifications

Color	red
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	tin-plated (galvanic)
Components	free from silicone and halogen

### Mechanical properties

#### Technical data

Sleeve length	14 mm
---------------	-------

### Environmental and real-life conditions

#### Ambient conditions

Permanent temperature	105 °C (-40 °C no load / 0 °C dynamic load)
Short-term temperature	120 °C

### Standards and regulations

# AI-TWIN 2X10 -14 RD - Ferrule

3201026

<https://www.phoenixcontact.com/us/products/3201026>



Design according to standard	DIN 46228-4, UL 486F-F
------------------------------	------------------------


# AI-TWIN 2X10 -14 RD - Ferrule

3201026

<https://www.phoenixcontact.com/us/products/3201026>



## Drawings



# AI-TWIN 2X10 -14 RD - Ferrule




3201026


<https://www.phoenixcontact.com/us/products/3201026>

## Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3201026>



**UL Listed**  
Approval ID: E488001



**cUL Listed**  
Approval ID: E488001



**cULus Listed**  
Approval ID: E488001

**cULus Listed**

# AI-TWIN 2X10 -14 RD - Ferrule



3201026

<https://www.phoenixcontact.com/us/products/3201026>

## Classifications

### ECLASS

ECLASS-11.0	27400201
ECLASS-12.0	27400201
ECLASS-13.0	27400201

### ETIM

ETIM 9.0	EC000005
----------	----------

### UNSPSC

UNSPSC 21.0	27121700
-------------	----------

# AI-TWIN 2X10 -14 RD - Ferrule



3201026

<https://www.phoenixcontact.com/us/products/3201026>

## Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

# AI-TWIN 2X10 -14 RD - Ferrule

3201026

<https://www.phoenixcontact.com/us/products/3201026>



## Accessories

### CRIMPFOX 16R TWIN - Crimping pliers

1212845

<https://www.phoenixcontact.com/us/products/1212845>



Crimping pliers, for TWIN ferrules according to UL 486F, three marked die stations, unlockable pressure lock, lateral entry

---

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)