

2393866-1 ✓ ACTIVE

LUMAWISE | ALR AA


TE Internal #: 2393866-1

ANSI Street Lighting Photocells, Americas, Electronic, 105 – 305 VAC, Commercial / Industrial, 1800 VA Load Rating (Ballast), Fixed Mount, ALR AA

[View on TE.com >](#)



Connectors > Lighting Connectors > Street Lighting Controls > ANSI Street Lighting Photocells



Lead Length: 193.04 mm [7.6 in]

Product Availability: **Americas**

Street Lighting Photo Control Technology: **Electronic**

Operating Voltage Range: **105 – 305 VAC**

Grade: **Commercial, Industrial**

Features

Product Type Features

Street Lighting Photo Control Technology	Electronic
--	------------

Configuration Features

Number of Positions	3
---------------------	---

Electrical Characteristics

Operating Voltage Range	105 – 305 VAC
-------------------------	---------------

Load Rating (Ballast)	1800 VA
-----------------------	---------

Load Rating (Tungsten)	1000 W
------------------------	--------

Fail Mode	On
-----------	----

Surge Protection	15 kA
------------------	-------

Operating Frequency	50 – 60 Hz
---------------------	------------

Relay Rating	30A General Purpose
--------------	---------------------

Body Features

Lead Length	193.04 mm[7.6 in]
-------------	-------------------

Primary Product Color	Black
-----------------------	-------



Mechanical Attachment

Mounting Options	Fixed Mount
------------------	-------------

Dimensions

MOV Diameter	20 mm
Wire Size	16 AWG
Product Length	58.5 mm[2.3 in]
Product Width	33 mm[1.29 in]

Usage Conditions

Operating Temperature Range	-40 – 70 °C[-40 – 158 °F]
-----------------------------	---------------------------

Operation/Application

Turn OFF Time Delay	2 – 5 seconds
Turn ON Light Level	1.5 fc
Turn ON Time Delay	Instant On seconds

Industry Standards

Approved Standards	ANSI C136.24
--------------------	--------------

Product Availability

Product Availability	Americas
----------------------	----------

Other

Grade	Commercial, Industrial
OFF/ON Ratio	1.5:1

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) SVHC > Threshold: Cd (7.5% in Component Part)

Article Safe Usage Statements:

Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2324697-2
PUSH GRIP CONNECTOR 2P



TE Part # 2324697-3
PUSH GRIP CONNECTOR 3P



TE Part # 2324697-4
PUSH GRIP CONNECTOR 4P




TE Part # 2324697-5
PUSH GRIP CONNECTOR 5P



TE Part # 2324697-6
PUSH GRIP CONNECTOR 6P

Also in the Series | ALR AA



ANSI Street Lighting Photocells(9)



Documents

Product Drawings

[ALR-AA-2000EL Photocontrol](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_2393866-1_1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2393866-1_1.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2393866-1_1.3d_igs.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[LUMAWISE ALR AA Series](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL](#)

English