

Features

- Suitable for Han D[®] / DD[®] inserts
- Can be combined with standard crimp contacts in one connector if needed
- Iron and constantan contacts according to IEC 60584 type J
- According to EUROMAP 14, Part 1

Technical characteristics

Contact resistance	≤1 mΩ
Material (contacts)	Iron, Constantan

Specifications and approvals





EN 60664-1
IEC 61984

Details

Crimping tools see chapter 90

Remarks on the crimp technique

The wire gauges mentioned in the catalogue refer to geometric wire gauges of cables.

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
Han D [®] , Crimp contact, Iron Contact surface: Gold plated 	0,14 ... 0,37	09 15 000 6171	09 15 000 6271	 <p>Stripping length 8 mm</p>
Han D [®] , Crimp contact, Constantan 	0,14 ... 0,37	09 15 000 6161	09 15 000 6261	 <p>Stripping length 8 mm</p>