


SCR31B-105-1R4A055JH

Aliases (UALF11R4A055JH)

KEMET, SCR31, AC Line Filters, Common Mode, 5.5 mH



Click [here](#) for the 3D model.

Dimensions

| | |
|-----------|------------|
| D | 48mm MAX |
| T | 42mm MAX |
| H | 35mm MAX |
| LL | 4mm +/-1mm |
| S | 17mm NOM |
| S1 | 30mm NOM |
| Wire Size | 1.4mm |

Packaging Specifications

| | |
|--------------------|------|
| Packaging | Tray |
| Packaging Quantity | 80 |
| Component Weight | 84 g |

General Information

| | |
|---------------|------------------------------|
| Series | SCR31 |
| Style | Through-Hole |
| Features | High Impedance, Space Saving |
| RoHS | Yes |
| Miscellaneous | 80 (K) Temperature Rise Max. |
| Core | Mn-Zn Ferrite |

Specifications

| | |
|-------------------|------------|
| Voltage AC | 500 VAC |
| Inductance | 5500 uH |
| Current | 10.5 A |
| Temperature Range | -25/+120°C |
| DC Resistance | 22 mOhms |