



Modular High Current Connector System

Identification	Part-Number		Drawings	Dimensions in mm
	Male insert (M)	Female insert (F)		
Han® HC module 650 Crimp terminal	09 11 001 3012	09 11 001 3112		

Identification	Wire gauge mm <sup>2</sup>	Part-Number		Drawings	Dimensions in mm																					
		Male contacts (M)	Female contacts (F)																							
Crimp contacts* Silver plated																										
	70	09 11 000 6161	09 11 000 6261		<table border="1"> <thead> <tr> <th>Wire gauge</th> <th>Ø in mm</th> <th>Strip-ping length</th> </tr> </thead> <tbody> <tr> <td>70 mm<sup>2</sup></td> <td>11.5</td> <td>42 mm</td> </tr> <tr> <td>95 mm<sup>2</sup></td> <td>13.5</td> <td>42 mm</td> </tr> <tr> <td>120 mm<sup>2</sup></td> <td>15.5</td> <td>42 mm</td> </tr> <tr> <td>150 mm<sup>2</sup></td> <td>17</td> <td>42 mm</td> </tr> <tr> <td>185 mm<sup>2</sup></td> <td>19</td> <td>42 mm</td> </tr> <tr> <td>240 mm<sup>2</sup></td> <td>21.5</td> <td>46 mm</td> </tr> </tbody> </table>	Wire gauge	Ø in mm	Strip-ping length	70 mm <sup>2</sup>	11.5	42 mm	95 mm <sup>2</sup>	13.5	42 mm	120 mm <sup>2</sup>	15.5	42 mm	150 mm <sup>2</sup>	17	42 mm	185 mm <sup>2</sup>	19	42 mm	240 mm <sup>2</sup>	21.5	46 mm
Wire gauge	Ø in mm	Strip-ping length																								
70 mm <sup>2</sup>	11.5	42 mm																								
95 mm <sup>2</sup>	13.5	42 mm																								
120 mm <sup>2</sup>	15.5	42 mm																								
150 mm <sup>2</sup>	17	42 mm																								
185 mm <sup>2</sup>	19	42 mm																								
240 mm <sup>2</sup>	21.5	46 mm																								
	95	09 11 000 6162	09 11 000 6262																							
	120	09 11 000 6163	09 11 000 6263																							
	150	09 11 000 6164	09 11 000 6264																							
	185	09 11 000 6165	09 11 000 6265																							
	240	09 11 000 6168	09 11 000 6268																							

Han HC Modular

\* Crimp area acc. to DIN EN 46 235

Stock items in bold type