


### 7.2 mm Square Miniature Rotary DIP Switches





- Mounting space reduced by 50%, compared with 10 mm square types.
- Surface/through-hole mounting terminlas are available both Top and Side-actuated types.
- Gold-plated contacts ensure high reliability.
- Embossed 100 pcs reel type is recommended for flexible demand.







### ■List of Models

#### ● Tube Packaging



#### Through-hole mounting (3 × 3 Terminal)

Type			Top-actuated, Flat	Top-actuated, Extended-actuator	Side-actuated, Flat	Side-actuated, Extended-actuator
						
No. of switching positions	Quantity per tube	Output code				
10	Top :63 Side:60	BCD Decimal	<b>A6K-102RF</b>	<b>A6K-102RS</b>	<b>A6KV-102RF</b>	<b>A6KV-102RS</b>
16		BCD Hexadecimal	<b>A6K-162RF</b>	<b>A6K-162RS</b>	<b>A6KV-162RF</b>	<b>A6KV-162RS</b>

#### Through-hole mounting (5 × 2 Terminal)





Type			Top-actuated, Flat	Top-actuated, Extended-actuator	Side-actuated, Flat	Side-actuated, Extended-actuator
						
No. of switching positions	Quantity per tube	Output code				
10	Top :63 Side:60	BCD Decimal	<b>A6K-104RF</b>	<b>A6K-104RS</b>	<b>A6KV-104RF</b>	<b>A6KV-104RS</b>
16		BCD Hexadecimal	<b>A6K-164RF</b>	<b>A6K-164RS</b>	<b>A6KV-164RF</b>	<b>A6KV-164RS</b>

#### Surface mounting (3 × 3 Terminal)

Type			Top-actuated, Flat	Top-actuated, Extended-actuator
				
No. of switching positions	Quantity per tube	Output code		
10	63	BCD Decimal	<b>A6KS-102RF</b>	<b>A6KS-102RS</b>
16		BCD Hexadecimal	<b>A6KS-162RF</b>	<b>A6KS-162RS</b>



Note: There are not side-actuator types on surface mounting with 3 × 3 terminals.

#### Surface mounting (5 × 2 Terminal)



Type			Top-actuated, Flat	Top-actuated, Extended-actuator	Side-actuated, Flat	Side-actuated, Extended-actuator
						
No. of switching positions	Quantity per tube	Output code				
10	63	BCD Decimal	<b>A6KS-104RF</b>	<b>A6KS-104RS</b>	<b>A6KSV-104RF</b>	<b>A6KSV-104RS</b>
16		BCD Hexadecimal	<b>A6KS-164RF</b>	<b>A6KS-164RS</b>	<b>A6KSV-164RF</b>	<b>A6KSV-164RS</b>



● Embossed taping

Surface mounting (3 × 3 Terminal)

Type		Top-actuated, Flat				Top-actuated, Extended-actuator			
No. of switching positions	Output code								
		Quantity per reel	Standard reel	Quantity per reel	100 pcs reel	Quantity per reel	Standard reel	Quantity per reel	100 pcs reel
10	BCD Decimal	1450	A6KS-102RF-P	100	A6KS-102RF-R100	850	A6KS-102RS-P	100	A6KS-102RS-R100
16	BCD Hexadecimal		A6KS-162RF-P		A6KS-162RF-R100		A6KS-162RS-P		A6KS-162RS-R100

Surface mounting (5 × 2 Terminal)

Type		Top-actuated, Flat				Top-actuated, Extended-actuator			
No. of switching positions	Output code								
		Quantity per reel	Standard reel	Quantity per reel	100 pcs reel	Quantity per reel	Standard reel	Quantity per reel	100 pcs reel
10	BCD Decimal	1450	A6KS-104RF-P	100	A6KS-104RF-R100	850	A6KS-104RS-P	100	A6KS-104RS-R100
16	BCD Hexadecimal		A6KS-164RF-P		A6KS-164RF-R100		A6KS-164RS-P		A6KS-164RS-R100

Type		Side-actuated, Flat				Side-actuated, Extended-actuator			
No. of switching positions	Output code								
		Quantity per reel	Standard reel	Quantity per reel	100 pcs reel	Quantity per reel	Standard reel	Quantity per reel	100 pcs reel
10	BCD Decimal	750	A6KSV-104RF-P	100	A6KSV-104RF-R100	750	A6KSV-104RS-P	100	A6KSV-104RS-R100
16	BCD Hexadecimal		A6KSV-164RF-P		A6KSV-164RF-R100		A6KSV-164RS-P		A6KSV-164RS-R100

Note: Order in multiples of the package quantity.

■ Ratings/Characteristics

Rating (resistive load)	25 mA at 24 VDC 10 μA (minimum current) at 3.5 VDC	
Ambient operating temperature	-30 to +80°C at 60% max. (with no icing or condensation)	
Ambient operating humidity	35% to 95% (at +5 to +35°C)	
Insulation resistance	100 MΩ min. (at 250 VDC with insulation tester)	
Contact resistance (initial value)	200 mΩ max.	
Dielectric strength	Between terminals	250 VAC for 1 min
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude
Shock resistance	Malfunction	300 m/s <sup>2</sup> min.
Durability	Electrical	20,000 steps min.
Washing	Not possible	
Degree of protection	IEC IP60	
Operating torque	1.96 × 10 <sup>-2</sup> N·m {2 gf·m} max.	
Weight (See note.)	Through-hole mounting terminals	Top-actuated, flat: Approx. 0.4 g, Side-actuated, flat: Approx. 0.7 g
	Surface mounting terminals	Top-actuated, flat: Approx. 0.4 g, Side-actuated, flat: Approx. 0.4 g

Note: Add 0.03 g for the extended-actuator type of each model.

## ■Output Codes

### 10-position Models

Code Position	BCD Decimal code			
	1	2	4	8
0				
1	●			
2		●		
3	●	●		
4			●	
5	●		●	
6		●	●	
7	●	●	●	
8				●
9	●			●

### 16-position Models

Code Position	BCD Hexadecimal code			
	1	2	4	8
0				
1	●			
2		●		
3	●	●		
4			●	
5	●		●	
6		●	●	
7	●	●	●	
8				●
9	●			●
A		●		●
B	●	●		●
C			●	●
D	●		●	●
E		●	●	●
F	●	●	●	●

Note: "●" indicates that the internal switch is ON.


**Dimensions** (Unit: mm)

**Through-hole mounting terminals**

● **Top-actuated Flat Models with 3 × 3 Terminal Arrangement**

**A6K-102RF**


**A6K-162RF**



● **Top-actuated Extended-actuator Models with 3 × 3 Terminal Arrangement**

**A6K-102RS**


**A6K-162RS**



● **Side-actuated Flat Models with 3 × 3 Terminal Arrangement**

**A6KV-102RF**


**A6KV-162RF**



● **Side-actuated Extended-actuator Models with 3 × 3 Terminal Arrangement**

**A6KV-102RS**

**A6KV-162RS**




Note: Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.

● **Top-actuated Flat Models with 5 × 2 Terminal Arrangement**

**A6K-104RF**


**A6K-164RF**



● **Top-actuated Extended-actuator Models with 5 × 2 Terminal Arrangement**

**A6K-104RS**


**A6K-164RS**



● Side-actuated Flat Models with 5 x 2 Terminal Arrangement

A6KV-104RF


A6KV-164RF



● Side-actuated Extended-actuator Models with 5 x 2 Terminal Arrangement

A6KV-104RS

A6KV-164RS



Surface mounting terminals


● Top-actuated Flat Models with 3 x 3 Terminal Arrangement

A6KS-102RF

A6KS-102-RF-R100

A6KS-162RF

A6KS-162RF-R100




● Top-actuated Extended-actuator Models with 3 x 3 Terminal Arrangement

A6KS-102RS

A6KS-102-RS-R100

A6KS-162RS

A6KS-162RS-R100




● Top-actuated Flat Models With 5 x 2 Terminal Arrangement

A6KS-104RF

A6KS-104-RF-R100

A6KS-164RF

A6KS-164RF-R100




● Top-actuated Extended-actuator Models with 5 x 2 Terminal Arrangement

A6KS-104RS

A6KS-104-RS-R100

A6KS-164RS

A6KS-164RS-R100



Note: Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.


● Side-actuated Flat Models with 5 × 2 Terminal Arrangement

A6KSV-104RF

A6KSV-104-RF-R100

A6KSV-164RF

A6KSV-164RF-R100




● Side-actuated Extended-actuator Models with 5 × 2 Terminal Arrangement

A6KSV-104RS

A6KSV-104-RS-R100

A6KSV-164RS

A6KSV-164RS-R100




**Note:** Unless otherwise specified, a tolerance of  $\pm 0.4$  mm applies to all dimensions.

**Internal Connections**


**Contact Form (Top View)**

**Top-actuated Models with  
3 × 3 Terminal Arrangement  
Through-hole mounting terminals  
Surface mounting terminals**




**Side-actuated Models with  
3 × 3 Terminal Arrangement  
Through-hole mounting terminals  
Surface mounting terminals**

Actuator side (A6KV)




**Top-actuated Models with  
5 × 2 Terminal Arrangement  
Through-hole mounting terminals  
Surface mounting terminals**




**Side-actuated Models with  
5 × 2 Terminal Arrangement  
Through-hole mounting terminals**

Actuator side



**Side-actuated Models with  
5 × 2 Terminal Arrangement  
Surface mounting terminals**


Actuator side




**PCB Dimensions (Reference)** (Unit: mm)

**Top View**


**3 x 3 Terminal Arrangement**  
Through-hole mounting terminals  
(Top-actuated Models)




**3 x 3 Terminal Arrangement**  
Through-hole mounting terminals  
(Side-actuated Models)




**3 x 3 Terminal Arrangement**  
Surface mounting terminals  
(Top-actuated Models)




**5 x 2 Terminal Arrangement**  
Through-hole mounting terminals  
(Top-actuated Models)




**5 x 2 Terminal Arrangement**  
Through-hole mounting terminals  
(Side-actuated Models)



**5 x 2 Terminal Arrangement**  
Surface mounting terminals  
(Top-actuated Models)



**5 x 2 Terminal Arrangement**  
Surface mounting terminals  
(Side-actuated Models)



:Through hole and Pattern prohibited area

**Note:** Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.

**Precautions**

Be sure to read the Safety precautions common to all DIP Switches for correct use.

Please check each region's Terms & Conditions by region website.

**OMRON Corporation**  
Device & Module Solutions Company

**Regional Contact**

**Americas**  
<https://components.omron.com/us>  
**Asia-Pacific**  
<https://components.omron.com/ap>  
**Korea**  
<https://components.omron.com/kr>

**Europe**  
<https://components.omron.com/eu>  
**China**  
<https://components.omron.com.cn>  
**Japan**  
<https://components.omron.com/jp>

© OMRON Corporation 2007-2022 All Rights Reserved.  
In the interest of product improvement, specifications are subject to change without notice.

**Cat. No. A174-E1-08**  
1122 (0207)