

# MJE2955T (PNP), MJE3055T (NPN)

## Complementary Silicon Plastic Power Transistors

These devices are designed for use in general-purpose amplifier and switching applications.

### Features

- High Current Gain – Bandwidth Product
- These Devices are Pb-Free and are RoHS Compliant\*

### MAXIMUM RATINGS

| Rating                                                                                    | Symbol            | Value       | Unit                     |
|-------------------------------------------------------------------------------------------|-------------------|-------------|--------------------------|
| Collector–Emitter Voltage                                                                 | $V_{CEO}$         | 60          | Vdc                      |
| Collector–Base Voltage                                                                    | $V_{CB}$          | 70          | Vdc                      |
| Emitter–Base Voltage                                                                      | $V_{EB}$          | 5.0         | Vdc                      |
| Collector Current                                                                         | $I_C$             | 10          | Adc                      |
| Base Current                                                                              | $I_B$             | 6.0         | Adc                      |
| Total Device Dissipation<br>@ $T_C = 25^\circ\text{C}$<br>Derate above $25^\circ\text{C}$ | $P_D$<br>(Note 1) | 75<br>0.6   | W<br>W/ $^\circ\text{C}$ |
| Operating and Storage Junction<br>Temperature Range                                       | $T_J, T_{stg}$    | -55 to +150 | $^\circ\text{C}$         |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Safe Area Curves are indicated by Figure 1. Both limits are applicable and must be observed.

### THERMAL CHARACTERISTICS



| Characteristics                      | Symbol          | Max  | Unit                      |
|--------------------------------------|-----------------|------|---------------------------|
| Thermal Resistance, Junction-to-Case | $R_{\theta JC}$ | 1.67 | $^\circ\text{C}/\text{W}$ |



ON Semiconductor®

[www.onsemi.com](http://www.onsemi.com)

## 10 AMPERE COMPLEMENTARY SILICON POWER TRANSISTORS 60 VOLTS – 75 WATTS



TO-220  
CASE 221A-09  
STYLE 1

### MARKING DIAGRAM



MJExx55T = Device Code  
xx = 29 or 30  
G = Pb-Free Package  
A = Assembly Location  
Y = Year  
WW = Work Week

### ORDERING INFORMATION

| Device    | Package             | Shipping        |
|-----------|---------------------|-----------------|
| MJE2955TG | TO-220<br>(Pb-Free) | 50 Units / Rail |
| MJE3055TG | TO-220<br>(Pb-Free) | 50 Units / Rail |

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

## MJE2955T (PNP), MJE3055T (NPN)

### ELECTRICAL CHARACTERISTICS (T<sub>C</sub> = 25°C unless otherwise noted)

| Characteristic                                                                                                                                                               | Symbol                | Min       | Max        | Unit |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------|------------|------|
| <b>OFF CHARACTERISTICS</b>                                                                                                                                                   |                       |           |            |      |
| Collector–Emitter Sustaining Voltage (Note 2)<br>(I <sub>C</sub> = 200 mAdc, I <sub>B</sub> = 0)                                                                             | V <sub>CEO(sus)</sub> | 60        | –          | Vdc  |
| Collector Cutoff Current<br>(V <sub>CE</sub> = 30 Vdc, I <sub>B</sub> = 0)                                                                                                   | I <sub>CEO</sub>      | –         | 700        | μAdc |
| Collector Cutoff Current<br>(V <sub>CE</sub> = 70 Vdc, V <sub>EB(off)</sub> = 1.5 Vdc)<br>(V <sub>CE</sub> = 70 Vdc, V <sub>EB(off)</sub> = 1.5 Vdc, T <sub>C</sub> = 150°C) | I <sub>CEX</sub>      | –<br>–    | 1.0<br>5.0 | mAdc |
| Collector Cutoff Current<br>(V <sub>CB</sub> = 70 Vdc, I <sub>E</sub> = 0)<br>(V <sub>CB</sub> = 70 Vdc, I <sub>E</sub> = 0, T <sub>C</sub> = 150°C)                         | I <sub>CBO</sub>      | –<br>–    | 1.0<br>10  | mAdc |
| Emitter Cutoff Current<br>(V <sub>BE</sub> = 5.0 Vdc, I <sub>C</sub> = 0)                                                                                                    | I <sub>EBO</sub>      | –         | 5.0        | mAdc |
| <b>ON CHARACTERISTICS</b>                                                                                                                                                    |                       |           |            |      |
| DC Current Gain (Note 2)<br>(I <sub>C</sub> = 4.0 Adc, V <sub>CE</sub> = 4.0 Vdc)<br>(I <sub>C</sub> = 10 Adc, V <sub>CE</sub> = 4.0 Vdc)                                    | h <sub>FE</sub>       | 20<br>5.0 | 100<br>–   | –    |
| Collector–Emitter Saturation Voltage (Note 2)<br>(I <sub>C</sub> = 4.0 Adc, I <sub>B</sub> = 0.4 Adc)<br>(I <sub>C</sub> = 10 Adc, I <sub>B</sub> = 3.3 Adc)                 | V <sub>CE(sat)</sub>  | –<br>–    | 1.1<br>8.0 | Vdc  |
| Base–Emitter On Voltage (Note 2)<br>(I <sub>C</sub> = 4.0 Adc, V <sub>CE</sub> = 4.0 Vdc)                                                                                    | V <sub>BE(on)</sub>   | –         | 1.8        | Vdc  |
| <b>DYNAMIC CHARACTERISTICS</b>                                                                                                                                               |                       |           |            |      |
| Current–Gain–Bandwidth Product<br>(I <sub>C</sub> = 500 mAdc, V <sub>CE</sub> = 10 Vdc, f = 500 kHz)                                                                         | f <sub>T</sub>        | 2.0       | –          | MHz  |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

2. Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 20%.

# MJE2955T (PNP), MJE3055T (NPN)




Figure 1. Active-Region Safe Operating Area

There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown. Safe operating area curves indicate  $I_C - V_{CE}$  limits of the transistor that must be observed for reliable operation; i.e., the transistor must not be subjected to greater dissipation than the curves indicate.

The data of Figure 1 is based on  $T_{J(pk)} = 150^\circ\text{C}$ .  $T_C$  is variable depending on conditions. Second breakdown pulse limits are valid for duty cycles to 10% provided  $T_{J(pk)} \leq 150^\circ\text{C}$ . At high case temperatures, thermal limitations will reduce the power that can be handled to values less than the limitations imposed by second breakdown.




Figure 2. DC Current Gain




Figure 3. Power Derating





Figure 4. "On" Voltages

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at [www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)

