



NOTES:

1. OPERATION

1. GENTLY LIFT LATCH AT SIDE OF CONNECTOR.
2. SWING COVER OFF OF CONTACTS.
3. SLIDE THE FLEX TAPE INTO THE CONNECTOR PLACING THE EDGE OF THE FLEX TAPE UNDER 2 HOLD DOWN TABS.
4. FOLD OVER THE COVER AND PRESS IN PLACE UNTIL THE LATCH IS FULLY ENGAGED.

2. LIMIT CURRENT TO A MAXIMUM OF 5 AMPS.

JKL PART NO.: ZCH-143HD-8I

| | | | | | | | | | | | |
|---|------------------------|-------------|--|--------------------------|--|-----------------|--|--------------------------|------------------------------------|-----------------|--|
| | | | METRIC  THIRD ANGLE PROJECTION | | DIMENSIONS ARE IN mm (INCHES) TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- REF. 2 PL +/- REF. ANGLE +/- | |  COMPONENTS CORPORATION | | | | |
| | | | | | TITLE NO SOLDER 8mm FLEX TAPE INPUT CONNECTOR | | | | | | |
| A ADD SIDE VIEW RELEASE & CANCEL PL-1409-03 | | | 8/20/15 10/10/14 | DRAWN BY L. WENGSTROM | APPV'D BY L.R. | DATE 8/20/15 | SIZE A | FSCM NO. 55335 | DRAWING NO. ZCH-143HD-8I | | |
| REV. NO. | DESCRIPTION/ECO NUMBER | APPV'D DATE | - CAD DRAWING - MANUAL REVISIONS NOT PERMITTED | | | SCALE NONE | RELEASED DATE 10/10/14 | REVISION DATE 8/20/15 | REV. NO. A | SHEET 1 OF 1 | |