


Low Profile Rotary Position Sensor / Potentiometer

The N-15 series offers you endless rotation, 340° wide electrical angle, SMD or through-hole mount, an extended working temperature range of -40° C to $+120^{\circ}$ C and a whole series of customisation possibilities making it the most flexible product on the market. The N-15 is ideal for appliance and automotive control and sensor applications.











KEY FEATURES

- ▶SMD or Through-hole mount
- ► Excellent performance (3% linearity)
- ▶ Up to 2.000.000 life cycles
- ▶ IP54 protection
- ▶360° endless rotation
- ▶340° electrical angle
- ► Low profile (4.4 mm) and footprint (15 mm)
- ▶ High operating temperature range
- ▶ Polarised "T" rotor (European Home Appliance standard)
- ▶ Embossed tape packaging according to IEC 60286-3:2007
- ► All PT-15 shafts compatible

Also available as 6-pulse incremental encoder or mechanical switch with up to 12 positions.

ELECTRICAL SPECIFICATIONS

	Standard	Extra-long life	
Taper	Linear		
Resistance range ¹	5 kΩ ≤ Rn ≤ 100 kΩ	5 kΩ	
Tolerance	±30%		
Max. voltage	120 Vdc	27 Vdc	
Nominal power at 50°C (122°F)	0.15 W		
Linearity (absolute)	3%		
Operating temperature	-40°C to +120°C		

¹ Others check availability

APPLICATIONS

Appliances

- ▶ Timer and program selection
- ▶ Temperature controls

Automotive

- ► HVAC control
- ▶ Seat position
- ▶ Mirror actuator feedback
- ► Gear Shift Position

Size and position detectors

MECHANICAL SPECIFICATIONS

	Standard	Extra-long life		
Mechanical rotation angle	360°			
Electrical rotation angle	340° ±10° 110° ±10°			
Rotational torque	≤20 mN.m			
Mounting method	SMD or Through-hole	SMD		
Mechanical life	Up to 200,000 cycles	Up to 2,000,000 cycles		

Low Profile Rotary Position Sensor / Potentiometer


ENVIRONMENTAL TESTING

	Test method	ΔR(%)- typical test results
Electrical life	1.000 h at 50°C; 0.15 W	±40%
Mechanical life	100,000 cycles at 20 cpm	±40% (Rn < 100 k)
Temperature coefficient	-40°C; +120°C	±300 ppm/°C (Rn < 100 k)
Thermal cycling	10h at 120°C and 10h at -40°C	±40%
Damp heat	480h at 40°C and 95% relative humidity (RH)	±40%
Storage	6 month at 23°C ±2°C and 50% RH	±40%


Out of range values may not comply with these results. Standard test conditions: temperature:23°C ±2°C and 45% to 70% RH

RECOMMENDED CONNECTIONS


Recommended connection circuit for a position sensor or control application (voltage divider circuit electronic design).



POWER RATING CURVE




RECOMMENDED REFLOW PROFILE



The recommended reflow profile is provided as a guideline. Optimal profile may differ due to oven type, assembly layout or other design or process variables. Customers should verify actual device performance in their specific application and reflow process. Please contact Piher if you require additional support.

Low Profile Rotary Position Sensor / Potentiometer




- 1. Mounting method: Horizontal adjust versions will be studied case by case.
- 2. Ω Value: \underline{XXX} First two digits of Ω -value; \underline{XXX} Number of zeros
- 3. A wide range of custom tapers and step curves is available on request.
- 4. Other tolerances and optional precision laser-trimmed voltage divider calibration available.

For Switch (S-15) and Incremental Encoder (E-15) versions see below or contact Piher Sensing Systems.

STANDARD RESISTANCE-VALUES								
Resistance Ω	5k	10k	20k	22k	25k	47k	50k	100k
Order Code	502	103	203	223	253	473	503	104

DIMENSIONS

SMD mount



Low Profile Rotary Position Sensor / Potentiometer

DIMENSIONS Through-hole mount 1.2±0.50 4.05±0.05 12.5±0.20 $4.4_{-0.20}^{+0.30}$ 8.5±0.20 Ø6.29 (WITHOUT SOLDER MASK) 12.5 ± 0.50 XXX XXX 15-0.50 12.5±0.50 1.2±0.50 6±0.20 SOLDER MASK PCB HOLE LAYOUT 1 PCB HOLE LAYOUT 2 ø1.3^{+0.10} ø7.5^{+0.10} 12.5 Recommended PCB hole diameter when using listed Piher shafts Horizontal adjust - vertical mount 1.2±0.5 28 PIHER 1.3+0.2 4.05±0.05 4.4-0.3 12.5±0.2 $\overline{\lambda\lambda\lambda}$ $\overline{\chi\chi\chi}$ SOLDER 15-0.5 DATE

STANDARD WIPER POSITION



VALUE

Rotary Switch (S-15) and Incremental Encoder (E-15)

ROTARY SWITCH S-15 Standard specifications 2-position switch 6-position switch Switch Positions Closed contact resistance < 5 Ω Open contact resistance $\rightarrow 10 \text{ m}\Omega$ Contact current 10μA - 100mA 16 Vdc Operating voltage 13.5 ±0.2 Vdc -40°C to +85°C Temperature range < 2 Ncm Rotational torque 360° (endless rotation) Mechanical rotational angle Mechanical life 15K cycles 35K cycles

For more information on switch sequence, dimensions, packaging or ordering code, please contact Piher Sensing Systems.

INCREMENTAL ENCODER E-15 Standard specifications 3-pulse encoder 6-pulse encoder ON (E-S)(E-S)OFF Graph Code |CW| ON ON (A-S)(A-S)P. 0 < 5 Ω Closed contact resistance > 10 mΩ Open contact resistance Contact current 10μA - 100mA 13.5 ±0.2 Vdc Operating voltage 16 Vdc -40°C to +120°C Temperature range < 2 Ncm Rotational torque 360° (endless rotation) Mechanical rotational angle Mechanical life 10K cycles 36K cycles

For more information on packaging options or ordering code, please contact Piher Sensing Systems.

Low Profile Rotary Position Sensor / Potentiometer

SHAFTS Hollow shafts models Solid shafts models Ø 6 ø6 Fig. Ref. В 5272 12 Ref. 5214 9 15 2 19 5219 15 9 5 5208 9.5 5.5 6.5 7 5220 16.8 9 9 5216 31 35 8 5207 25.3 9 10 5218 37.8 9 33.8 12 5227 46 5 5209 11 35 31 Slot (1 x 1.4) perpendicular to wiper position. A = Length measured from rotor surface Fig. 12 slot is on line with wiper position. B = Knurling length C = Hollow depth Fig. 3 - Ref. 5372 Fig. 18 - Ref. 5271 Fig. 15 - Ref. 5217 Fig. 17 - Ref. 5210 Fig. 19 - Ref. 6032* Fig. 20 - Ref. 5369* Ø6 Ø 5.9 Ø4 Ø4 2 28.7 Fig. 21 - Ref. 6031* Fig. 22 - Ref. 6029 Fig. 23 - Ref. 6022 Fig. 29 - Ref. 6162 Fig. 25 - Ref. 6059 Fig. 27 - Ref. 5268* Ø4 _ Ø6 | Ø6 Ø 6 Fig. 28 - Ref. 6055 Ø6 Shafts must be ordered separately and are delivered unassembled. *Not available in self-extinguishable plastic.

Low Profile Rotary Position Sensor / Potentiometer


PACKAGING

Through-hole models - bulk (150 units per box)



Dimensions (mm): 185x85x40

SMD model - embossed tape (500 pcs/reel)



Bulk packaging for SMD models available on request.

OUR ADVANTAGE

- ▶ Leading-edge innovative position sensing solutions
 - Contactless (Hall-effect and Inductive Technology)
 - Contacting (Potentiometers, Printed Electronics)
- ► Engineering design-in support
- ▶ All our products can be customized to fit target application and customer requirement
- Capability to move seamlessly from development to true high-volume production
- ▶ A global footprint with global engineering and commercial support
- ▶ One-stop shop not limited to position sensors (temperature, pressure, gas,...) through group collaboration
- ▶ Flexibility and entrepreneurship of a medium-sized company with the backing of Amphenol Corporation









Please always use the latest updated datasheets and 3D models published on our website.

Disclaimer:
The product information in this catalog is for reference purposes. Please consult for the most up to date and accurate design information.
Piher Sensors & Controls S.A., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Piher"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product described herein or behalf (sold in the liability arising out of the use or application of any product described herein or any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Piher's terms and conditions of sale, including but not limited to the warranty expressed therein, which

apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Piher.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or sellling Piher products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Piher for any damages arising or resulting for such use or sale. Please contact authorized Piher personnel to obtain written terms and conditions regarding products designed for such applications. Product names and markings noted herein may be trademarks of their respective owners. Information contained in and/or attached to this catalog may be subject to export control regulations of the European Community, USA, or other countries. Each recipient of this document is responsible to ensure that usage and/or transfer of any informat contained in this document complies with all relevant export control regulations. If you are in any doubt about the export control restrictions that apply to this information, please contact the sender immediately. For any Piher Exports, Note: All products? technologies are EAR9? Classified commodities. Exports from the United States are in accordance with the Export Administration Regulations. Diversion contrary to US law is prohibited.

CONTACT

Piher Sensing Systems Polígono Industrial Municipal Vial T2, Nº22

31500 Tudela Spain

sales@piher.net

+34 948 820 450 Europe: Americas: +1 636 251 0855 Asia Pacific: +65 9641 8886 +91 9538 686 586 India:

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

 XEJPL5220CR
 N15TS-502A3030
 N15TS-104A3030
 N15TS-103A3030
 XEJPL5207CR
 XEJPL5272CR

 XEJPL5214CR
 XEJPL5208CR
 JPEPL5227IN
 5219NE
 JPEPL5220CR
 JPEPL5214IN
 JPEPL5272INI

 JPEPL6022NE
 XEJPL5219NE
 JPEPL6053NE