



3M™ 1200E Series Safety Spectacles

Product Description

The 3M™ 1200E Series Safety Spectacles offer the best of both robust protection and style. The wrap-around design provides excellent side protection and helps to maintain a fashionable appearance. These products are available with either a clear or grey lens (protection from sun glare).

Product Range

71509-00000M 3M™ 1200E (clear lens)

71509-00001M 3M™ 1200E (grey lens)

Intended Use

These products are intended for protection against high speed particles at low energy (F) at extreme temperature conditions, -5°C and +55°C, (T) in accordance with EN166:2001. They also protect against UV radiation in accordance with EN170:2002, and sun glare in accordance with EN172:1994 (grey lenses only).

Key Features

- Optical class 1 lens suitable for prolonged use.
- Design provides excellent coverage and good field of vision
- Highly fashionable design
- Lightweight (28g) for maximum comfort
- Offers excellent protection against UV radiation
- Lens coatings provide both scratch resistance and reduced fogging
- Adjustable soft nose piece for improved comfort and an optimised fit

Applications

These products can be used in a wide range of applications including:

- Construction
- Electronic component manufacture
- General assembly
- General laboratory
- Light duty maintenance and repair
- Pharmaceutical

Standards and Approval

This protective eyewear has been shown to meet the basic safety requirements under Article 10 of the European Community Directive 89/686/EEC and is thus CE marked.

These products have been examined at the design stage by INSPEC International Ltd., 56 Leslie Hough Way, Salford, Greater Manchester, M6 6AJ, United Kingdom (Notified Body number 0194).

These products are tested and CE approved against EN166:2001.

Marking

The products have demonstrated compliance with the requirements of EN 166:2001 and associated standards and bear the following marks:

Clear lens	2C-1.2 3M 1 FT
Grey lens	5-3.1 3M 1 FT
Frames	3M 1200E EN166 FT CE

Materials Listing

Component	Material
Lens	Polycarbonate
Brow	High Impact Polyamide (Nylon)
End-pieces	High Impact Polyamide (Nylon)
Temples	Polycarbonate and polyester blend
Nose Piece	Thermoplastic Elastomer with Brass adjustable core

Use Limitation

- Never modify or alter this product
- Do not use this product against hazards other than those specified in this document.
- This product is not suitable for grinding or welding
- In accordance with EN166:2001 safety spectacles cannot be tested and approved for use against liquid droplets. Where liquid protection is specified a suitable product should be considered, for example safety goggles.
- This product is not designed to be worn over prescription spectacles

Explanation of Marking

Marking	Description
2C-1.2 (EN 170:2002)	UV protection with good colour recognition. This product conforms to the requirements of the standard, providing UV protection for the complete specified range (210nm – 365nm).
5-3.1 (EN 172:1994 (as amended))	Sun-glare protection conforming to the requirements of the standard, providing UV protection for the complete specified range (280nm – 350nm).
1	Optical class
F	Impact protection against high speed particle at low energy (45m/s)
T	Tested for impact protection at extreme temperature conditions -5°C and +55°C

Important Notice

3M does not accept liability of any kind, be it direct or consequential (including, but not limited to, loss of profits, business and/or goodwill) arising from reliance upon any information herein provided by 3M. The user is responsible for determining the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence.



Personal Safety Division
EMEA Region
 3M Centre,
 Cain Road, Bracknell
 Berkshire RG12 8HT
 United Kingdom
 Tel: +44 (0) 1344 858000
www.3M.eu/safety

15795
 3M is a trademark of 3M company.
 Please recycle. © 3M 2013.
 All rights reserved.