

2373921-3 ✓ ACTIVE

DEUTSCH | DEUTSCH NTSEAL


TE Internal #: 2373921-3

Other Automotive Connector Accessories, Blind Plug, PBT, Blue,  
-40 – 125 °C [-40 – 257 °F], DEUTSCH NTSEAL

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Connector Accessories > Other Automotive Connector Accessories



Automotive Connector Accessory Type: **Blind Plug**

Primary Product Material: **PBT**

Primary Product Color: **Blue**

Operating Temperature Range: **-40 – 125 °C [-40 – 257 °F]**

## Features

### Product Type Features

Automotive Connector Accessory Type	Blind Plug
-------------------------------------	------------

### Body Features

Primary Product Material	PBT
Primary Product Color	Blue

### Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC



Halogen Content Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability Not reviewed for solder process capability

**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


### Compatible Parts

 <p>TE Part # 2366509-1 48POS, HYBRID, PIN HSG ASSY, SLD, COD A</p>	 <p>TE Part # 2-2366509-1 48POS, HYBRID, PIN HSG ASSY, SLD, COD A</p>	 <p>TE Part # 2-2366509-2 48POS, HYBRID, PIN HSG ASSY, SLD, COD B</p>	 <p>TE Part # 2-2366509-3 48POS, HYBRID, PIN HSG ASSY, SLD, COD C</p>
 <p>TE Part # 2-2366509-4 48POS, HYBRID, PIN HSG ASSY, SLD, COD D</p>	 <p>TE Part # 2366494-1 48POS, HYBRID, SOC HSG ASSY, SLD, COD A</p>	 <p>TE Part # 2366494-2 48POS, HYBRID, SOC HSG ASSY, SLD, COD B</p>	 <p>TE Part # 2366494-3 48POS, HYBRID, SOC HSG ASSY, SLD, COD C</p>
 <p>TE Part # 2366494-4 48POS, HYBRID, SOC HSG ASSY, SLD, COD D</p>	 <p>TE Part # 2366509-2 48POS, HYBRID, PIN HSG ASSY, SLD, COD B</p>	 <p>TE Part # 2366509-3 48POS, HYBRID, PIN HSG ASSY, SLD, COD C</p>	 <p>TE Part # 2366509-4 48POS, HYBRID, PIN HSG ASSY, SLD, COD D</p>

Also in the Series | **DEUTSCH NTSEAL**



Automotive Connector Caps & Covers (5)



Automotive Housings(37)



Automotive Seals & Cavity Plugs(2)



Other Automotive Connector Accessories(5)

## Customers Also Bought



TE Part #DT04-12PD  
REC, 12P, BRN, N, D



TE Part #2112295-1  
PROTECTION CAP, GROUP D, ASSY



TE Part #2366509-1  
48POS, HYBRID, PIN HSG ASSY, SLD,  
COD A



TE Part #2366517-2  
FIX RING, CONN KIT



TE Part #3-1418883-1  
62.POS.MIXED REC.HSG



TE Part #2-2366509-1  
48POS, HYBRID, PIN HSG ASSY, SLD,  
COD A



TE Part #2366494-1  
48POS, HYBRID, SOC HSG ASSY, SLD,  
COD A



TE Part #2366517-1  
FIX RING, CONN KIT



TE Part #2373921-4  
CVTY PLUG, PIN DIA 1.6, CVTY DIA, 2.0,  
GRN



TE Part #2378521-1  
BACKSHELL, CONN KIT

## Documents

### Product Drawings

[CVTY PLUG, PIN DIA 2.5, CVTY DIA, 2.5, BLU](#)

English

### CAD Files

[3D PDF](#)

3D

### Customer View Model

[ENG\\_CVM\\_CVM\\_2373921-3\\_A.2d\\_dxf.zip](#)



English

Customer View Model

[ENG\\_CVM\\_CVM\\_2373921-3\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2373921-3\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Product Specifications**

[Application Specification](#)

English