



NOTES:

- ① HOUSING MAT'L: HIGH TEMPERATURE THERMOPLASTIC. UL94V-0.
COLOR : BLACK
- ② PIN MATERIAL: PHOSPHOR-BRONZE
- ③ 3 LBS/1.36 KG MIN. RETENTION.
- ④ TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS.
EXAMPLE: 10 POS., (N-1) x .100[2.54]=900[22.87]
- ⑤ RETENTIVE LEG:
RETENTIVE LEG APPLICABLE TO TAIL LENGTH .120/3.05 ONLY.
RETENTION IS APPLIED TO FOUR PINS ON PART SIZES OF 2x1.4 AND SMALLER,
AND APPLIED TO EIGHT PINS ON PARTS SIZES OF 2x1.5 AND LARGER.
SLR 2.3KG MAX INSERTION FORCE AND .25LB./1KG MIN RETENTION FORCE
PER RETENTIVE PIN USING .062/1.57 THICK CIRCUIT BOARD AND RECOMMENDED
HOLE PATTERN. RETENTIVE LOCATION AT THE DISCRETION OF THE MANUFACTURER.
OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE.
- 6. PACKAGED IN TRAYS.
- 7. UNDERPLATING: 50µ"/1.27µm Ni.
- ⑧ FOR POLARIZATION, SPECIFY POSITION NUMBER (i.e., 03= PIN 3) TO OMIT PIN.
OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE.
- ⑨ ADD "L" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- ⑩ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- 11. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm
MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES
IF THEY ARE AVAILABLE.
THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 20 SECONDS IN A CONNECTION, INFRA-RED OR VAPOR PHASE REFLOW
OVEN. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.



mat'l code		surface		tolerance		projection		product family	
ISO 802		ISO 406		ISO 100		INCH/MM		QUICKIE	
ISO 100		ISO 406		ISO 100		scale 1:1		title	
ISO 100		ISO 406		ISO 100		scale 1:1		.100/2.54cc EJECT LATCH	
ISO 100		ISO 406		ISO 100		scale 1:1		SHOROUNDED VERTICAL HEADER	
ISO 100		ISO 406		ISO 100		scale 1:1		dwg no	
ISO 100		ISO 406		ISO 100		scale 1:1		53611	
ISO 100		ISO 406		ISO 100		scale 1:1		sheet 2 of 2 size	
ISO 100		ISO 406		ISO 100		scale 1:1		A3	
ISO 100		ISO 406		ISO 100		scale 1:1		type	
ISO 100		ISO 406		ISO 100		scale 1:1		Product Customer Drawing	
ISO 100		ISO 406		ISO 100		scale 1:1		sheet	
ISO 100		ISO 406		ISO 100		scale 1:1		revision	
ISO 100		ISO 406		ISO 100		scale 1:1		sheet	
ISO 100		ISO 406		ISO 100		scale 1:1		index	