# Schottky Power Rectifier, Surface Mount

1.0 A, 30 V, SOD-123 Package

This device uses the Schottky Barrier principle with a large area metal-to-silicon power diode. Ideally suited for low voltage, high frequency rectification or as free wheeling and polarity protection diodes in surface mount applications where compact size and weight are critical to the system. This package also provides an easy to work with alternative to leadless 34 package style. Because of its small size, it is ideal for use in portable and battery powered products such as cellular and cordless phones, chargers, notebook computers, printers, PDAs and PCMCIA cards. Typical applications are AC-DC and DC -DC converters, reverse battery protection, and "Oring" of multiple supply voltages and any other application where performance and size are critical.

### Features

- Guardring for Stress Protection
- Low Forward Voltage
- 125°C Operating Junction Temperature
- Epoxy Meets UL 94 V-0
- Package Designed for Optimal Automated Board Assembly
- ESD Ratings: Machine Model, C
  - Human Body Model, 3B
- NRVB Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC–Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

### **Mechanical Characteristics**

- Reel Options: MBR130LSFT1G = 3,000 per 7 in reel/8 mm tape
- Device Marking: L3L
- Polarity Designator: Cathode Band
- Weight: 11.7 mg (approximately)
- Case: Epoxy, Molded
- Lead Finish: 100% Matte Sn (Tin)
- Lead and Mounting Surface Temperature for Soldering Purposes: 260°C Max. for 10 Seconds
- Device Meets MSL 1 Requirements



# **ON Semiconductor®**


http://onsemi.com

# SCHOTTKY BARRIER RECTIFIER 1.0 AMPERES, 30 VOLTS



SOD-123FL CASE 498

#### MARKING DIAGRAM



#### **ORDERING INFORMATION**

| Device        | Package                | Shipping <sup>†</sup> |
|---------------|------------------------|-----------------------|
| MBR130LSFT1G  | SOD-123FL<br>(Pb-Free) | 3000/Tape & Reel      |
| NRVB130LSFT1G | SOD-123FL<br>(Pb-Free) | 3000/Tape & Reel      |

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

### MAXIMUM RATINGS

| Rating  | Symbol   | Value      | Unit |
|---|--|------------|------|
| Peak Repetitive Reverse Voltage<br>Working Peak Reverse Voltage<br>DC Blocking Voltage                  | V <sub>RRM</sub><br>V <sub>RWM</sub><br>V <sub>R</sub> | 30         | V    |
| Average Rectified Forward Current (At Rated $V_R$ , $T_L$ = 117°C)                                      | Ι <sub>Ο</sub>   | 1.0        | А    |
| Peak Repetitive Forward Current (At Rated $V_R$ , Square Wave, 100 kHz, $T_L$ = 110°C)                  | I <sub>FRM</sub>                                       | 2.0        | A    |
| Non-Repetitive Peak Surge Current<br>(Non-Repetitive peak surge current, halfwave, single phase, 60 Hz) | I <sub>FSM</sub>                                       | 40         | A    |
| Storage Temperature   | T <sub>stg</sub>                                       | -55 to 150 | °C   |
| Operating Junction Temperature  | TJ   | -55 to 125 | °C   |
| Voltage Rate of Change (Rated $V_R$ , $T_J = 25^{\circ}C$ )   | dv/dt  | 10,000     | V/μs |

#### THERMAL CHARACTERISTICS

| P                  |                                 |                  |     |      |
|--------------------|---------------------------------|------------------|-----|------|
| Thermal Resistance | e, Junction-to-Lead (Note 1)    | R <sub>til</sub> | 26  | °C/W |
| Thermal Resistance | e, Junction-to-Lead (Note 2)    | R <sub>til</sub> | 21  |      |
| Thermal Resistance | e, Junction-to-Ambient (Note 1) | R <sub>tia</sub> | 325 |      |
| Thermal Resistance | e, Junction-to-Ambient (Note 2) | R <sub>tia</sub> | 82  |      |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

Mounted with minimum recommended pad size, PC Board FR4.
Mounted with 1 in. copper pad (Cu area 700 mm<sup>2</sup>).


### **ELECTRICAL CHARACTERISTICS**

| Maximum Instantaneous Forward Voltage (Note 3)                                | V <sub>F</sub> | T <sub>J</sub> = 25°C | T <sub>J</sub> = 100°C | V  |
|---|----------------|-----------------------|------------------------|----|
| $(I_F = 0.1 \text{ A})$<br>$(I_F = 0.7 \text{ A})$<br>$(I_F = 1.0 \text{ A})$ |                | 0.29<br>0.36<br>0.38  | 0.18<br>0.27<br>0.30   |    |
| Maximum Instantaneous Reverse Current (Note 3)                                | I <sub>R</sub> | T <sub>J</sub> = 25°C | T <sub>J</sub> = 100°C | mA |
| (V <sub>R</sub> = 30 V)   |                | 1.0                   | 25                     |    |


Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

3. Pulse Test: Pulse Width  $\leq$  250 µs, Duty Cycle  $\leq$  2%.

## **TYPICAL CHARACTERISTICS**



## **TYPICAL CHARACTERISTICS**





DATE 10 MAY 2013






Ε D POLARITY INDICATOR OPTIONAL AS NEEDED TOP VIEW





# RECOMMENDED SOLDERING FOOTPRINT\*



DIMENSIONS: MILLIMETERS

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

SOD-123FL **CASE 498** ISSUE D

Δ

END VIEW

NOTES:

- 1. 2.
- 3.
- LES: DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982. CONTROLLING DIMENSION: MILLIMETER. DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH. DIMENSIONS D AND J ARE TO BE MEASURED ON FLAT SECTION OF THE LEAD: BETWEEN 0.10 AND 0.25 MM FROM THE LEAD TIP. 4.

|     | MILLIMETERS |      |      | INCHES |       |       |
|-----|-------------|------|------|--------|-------|-------|
| DIM | MIN         | NOM  | MAX  | MIN    | NOM   | MAX   |
| Α   | 0.90        | 0.95 | 0.98 | 0.035  | 0.037 | 0.039 |
| A1  | 0.00        | 0.05 | 0.10 | 0.000  | 0.002 | 0.004 |
| b   | 0.70        | 0.90 | 1.10 | 0.028  | 0.035 | 0.043 |
| С   | 0.10        | 0.15 | 0.20 | 0.004  | 0.006 | 0.008 |
| D   | 1.50        | 1.65 | 1.80 | 0.059  | 0.065 | 0.071 |
| Е   | 2.50        | 2.70 | 2.90 | 0.098  | 0.106 | 0.114 |
| L   | 0.55        | 0.75 | 0.95 | 0.022  | 0.030 | 0.037 |
| ΗE  | 3.40        | 3.60 | 3.80 | 0.134  | 0.142 | 0.150 |
| θ   | 0°          | -    | 8°   | 0°     | _     | 8°    |

#### GENERIC **MARKING DIAGRAM\***



XXX = Specific Device Code = Date Code Μ -= Pb-Free Package

(Note: Microdot may be in either location)

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " •", may or may not be present.

| DOCUMENT NUMBER:  | 98AON11184D            | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |             |  |  |
|---|------------------------|---|-------------|--|--|
| DESCRIPTION:  | DESCRIPTION: SOD-123FL |   | PAGE 1 OF 1 |  |  |
| ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries.<br>ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others. |                        |   |             |  |  |

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor date sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use a a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor houteds for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

#### TECHNICAL SUPPORT

ON Semiconductor Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910 Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative