High Power Resistive Products

Resistors

AVX introduces its line of High Power Resistive Products. All products are designed and manufactured at our ISO 9001 Facilities.

ELECTRICAL SPECIFICATIONS


Resistance: 50 and 100 Ω standard (10 Ω - 200 Ω available) **Resistance Tolerance:** $\pm 5\%$ standard ($\pm 2\%$ available)

Power: 2 Watts through 250 Watts

Operating Temperature Range: -55°C to +150°C

Temperature Coefficient: < 150 ppm/°C

Low Capacitance



MECHANICAL SPECIFICATIONS

Package: Surface Mount Chips, Chips, Leaded Chips, Flanged

Substrate Material: Aluminum Nitride

Process: Thin Film

Resistive Material: Tantalum

Terminals: Silver **Cover:** Alumina

Mounting Flange: 100% Cu, Ni or Ag Plated


Mechanical Tolerance: ±0.13 (0.005)

SMT and Chip products, supplied on Tape and Reel

Non-Magnetic (exception RP4 and RP5 Style Surface Mount Resistors)

RoHS Compliant

POWER DERATING





High Power Resistive Products



Resistors

SURFACE MOUNT CHIP RESISTORS - RP4 AND RP5 SERIES

GENERAL SPECIFICATIONS

Resistance: 50 and 100 Ω standard (contact factory for custom resistance values)

Resistive Tolerance: ±2% standard

Operating Temp Range: -55°C to +150°C

Temperature Coefficient: <150 ppm/°C


Resistive Elements: Proprietary Thin Film

Substrate Material: Aluminum Nitride

Terminals: Silver over Nickel

RoHS Compliant

Tape and Reel Specifications: See Page 38




mm (inches)

| AVX Part Number* | W ±0.25 (0.010) | L ±0.25 (0.010) | T ±0.13 (0.005) | WT ±0.13 (0.005) | LT ±0.13 (0.005) | LA ±0.13 (0.005) | Capacitance (pF) | Power Max** (Watts) |
|---------------------|--------------------|--------------------|--------------------|---------------------|---------------------|---------------------|---------------------|------------------------|
| RP42010RxxxxGTTR | 2.54 (0.100) | 5.08 (0.200) | 1.02 (0.040) | 2.29 (0.090) | 0.76 (0.030) | 2.41 (0.095) | .95 pF | 10W |
| RP42525RxxxxGTTR | 6.22 (0.245) | 6.22 (0.245) | 1.02 (0.040) | 3.05 (0.120) | 1.02 (0.040) | 2.79 (0.110) | 1.85 pF | 20W |
| RP43725RxxxxGTTR | 6.35 (0.250) | 9.53 (0.375) | 1.02 (0.040) | 3.05 (0.120) | 1.27 (0.050) | 4.95 (0.195) | 3.0 pF | 30W |
| RP43737RxxxxGTTR | 9.40 (0.370) | 9.40 (0.370) | 1.02 (0.040) | 9.14 (0.360) | 1.27 (0.050) | 4.95 (0.195) | 3.5 pF | 40W |
| RP52010RxxxxGTTR | 2.54 (0.100) | 5.08 (0.200) | 1.02 (0.040) | 2.29 (0.090) | 0.76 (0.030) | - | - | 4W |
| RP52525RxxxxGTTR | 6.22 (0.245) | 6.22 (0.245) | 1.02 (0.040) | 3.05 (0.120) | 1.02 (0.040) | - | - | 6W |
| RP53725RxxxxGTTR | 6.35 (0.250) | 9.53 (0.375) | 1.02 (0.040) | 3.05 (0.120) | 1.27 (0.050) | - | - | 8W |
| RP53737RxxxxGTTR | 9.40 (0.370) | 9.40 (0.370) | 1.02 (0.040) | 9.14 (0.360) | 1.27 (0.050) | - | - | 10W |


^{*} xxxx denotes Ohm value.

HOW TO ORDER



Contact factory for custom ratings and sizes.

POWER DERATING





^{**} Test Condition: Chip soldered to a via patch on a 30-mil-thick Rogers RO4350 board; Land surfaces at 100°C; maximum rated power applied.