



A=2.54\* $n$ P $\pm$ 0.50  
 B=2.54\* $n$ P-2.54 $\pm$ 0.20  
 Pin Number=1~40

**Technical Data**  
 Material: Brass  
 Contact material: Brass  
 Plating: Gold Flash  
 Insulator material: Black polyester UL94V-0  
 Standard: PA6T+30%G.F

**Electrical:**  
 Current rating: 3Amps/contact  
 Contact resistance:  $\leq 20m\Omega$  /contact  
 Insulation resistance:  $\geq 1000M\Omega$  at V=100V  
 Withstanding voltage: 550V AC/minute

**Mechanical:**  
 Soldering temperature:  $+260^{\circ}C$ , 4s max  
 UNSPECIFIED TOLERANCE:  $\pm 0.20$



B TYPE

PCB Layout

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/7/17	D/2254S-11-XX-48	
CHECKED			ELECTRONICS CO.,LTD	
APPROVALS			CONNECTOR	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	UNIT:	SCALE:	SHEET	PROJ.
	A		NEW				30 $\pm$ 0.15 10 $\pm$ 0.10 5 $\pm$ 0.10	$\pm 0.30$ $\pm 0.20$ $\pm 0.15$	mm	1:1	1 OF 1	