



### **HYT 221**

# **Digital Humidity and Temperature Module**

## **Optimal for critical application areas**








#### Benefits & Characteristics

- Calibrated and temperature compensated
- High chemical resistance
- Wide humidity and temperature range
- Very stable at high humidity
- Mechanically robust

- Excellent humidity/temperature accuracy and stability
- I<sup>2</sup>C protocol (address 0x28 or alternative address)
- Very low drift
- Interchangeable without adjustments

#### Illustration<sup>1)</sup>





1) For actual size, see mechanical dimensions

#### Technical Data

Operating temperature range:	-40 °C to +125 °C
Operating humidity range:	0 % RH to 100 % RH
Hysteresis:	< ±1 % RH
Linearity error:	< ±1 % RH
Temperature error:	0.05 % RH/K (0 °C to +60 °C)
Operating voltage:	2.7 V to 5.5 V
Current consumption (nominal):	< 22 μA at 1 Hz measuring rate; 850 μA max.
Current consumption (sleep):	< 1 μΑ
Digital interface:	I <sup>2</sup> C, address 0x28 or alternative address
Operating voltage (limits):	-0.3 V to 6 V
Storage conditions:	-20 °C to +50 °C

	Humidity	Temperature
Accuracy:	±1.8 % RH at +23 °C (0 % RH to +90 % RH)	±0.2 K (0 °C to +60 °C)
Reproducibility:	±0.2 % RH	±0.1 K
Resolution:	0.02 % RH	+0.015 °C
Response time t <sub>63</sub> :	< 12 s with membrane filter	< 12 s with membrane filter
Long-term drift:	< 0.5 % RH/a	< 0.05 K/a
Measuring principle:	Capacitive polymer humidity sensor	PTAT (integrated)

DHHYT221\_E2.2 1/3





### **HYT 221**

## **Digital Humidity and Temperature Module**











#### Mechanical Dimensions



#### Pin Assignment



1	2	3	4
SDA	GND	VCC	SCL

#### **Order Information**

	HYT 221
Order code	150.00068

#### Additional Electronics

	Document name:
LabKit:	DHHYTLabKit_E
LCD module:	DHLCD-Modul_E

DHHYT221\_E2.2 2/3





## **HYT 221**



## **Digital Humidity and Temperature Module**



## **Optimal for critical application areas**

CONDUCTIVITY

Additional	<b>Documents</b>
------------	------------------

Document name:

Application Note: AHHYTM\_E







INNOVATIVE SENSOR TECHNOLOGY Innovative Sensor Technology IST AG, Stegrütistrasse 14, CH-9642 Ebnat-Kappel, Switzerland, Phone: +41 (0) 71 992 01 00 | Fax: +41 (0) 71 992 01 99 | E-mail: info@ist-ag.com | Web: www.ist-ag.com